




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		20240529	Initial Release	
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item (a) Lever: Thermoplastic (UL 94-HB), Black
- Item (b) Terminal body: Thermoplastic (UL 94V-0), Black
- Item (c) Terminal cover: Thermoplastic (UL94V-0), Black
- Item (d) Terminal: Copper alloy, Tin plated over Nickel plated
- Item (e) Switch pin: Copper alloy, Tin plated over Nickel plated
- Item (f) Detect pin: Copper alloy, Tin plated over Nickel plated

Electrical:

- Voltage rating: 300 VAC
- Current rating: 6A
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- Wire strip length: 8 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +105°C
- Critical dimension: ▲
- Matching Pin: D=1.0mm

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	GB001 Series with switch pin				DWG NO.	8GB0002-001	
PART NO.	GB001xx1x000G				CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance	
		Rhine 20250410	Rhine 20250410			X.	±0.50
						X.X	±0.30
						X.XX	±0.10
						X°	±1°