

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PoE+ Ethernet switch conforms to IEEE 802.3at. Includes four PoE+ ports and one standard RJ45 port, all with 10/100 Mbps speeds.

## Your advantages

- Wide-range power supply of 18 ... 57 V DC
- Autocrossing
- Wide temperature range -40 °C ... +75 °C
- Redundant power supply
- POE status LED per port
- Auto negotiation
- Automatic detection of IEEE 802.3at or 802.3af powered devices

## Commercial data

Item number	2891064
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN18
Product key	DNN115
GTIN	4046356764322
Weight per piece (including packing)	772 g
Weight per piece (excluding packing)	685 g
Customs tariff number	85176200
Country of origin	TW

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



## Technical data

### Dimensions

Width	55 mm
Height	117 mm
Depth	78 mm

### Notes

Notes on operation	Mode B PoE
Note on application	
Note on application	Only for industrial use
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area

### Material specifications

Housing material	Aluminum
------------------	----------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

### Interfaces

Ethernet	
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet RJ45
Transmission length	100 m (Between transmitter / receiver)
Signal LEDs	LINK/ACT, 100, POE
No. of channels	1 (RJ45 port)

Ethernet (PoE)	
Connection method	RJ45
Transmission speed	10/100 Mbps
Transmission physics	Ethernet RJ45
Transmission length	100 m (Between transmitter / receiver)
Signal LEDs	LINK/ACT, 100, POE
No. of channels	4 (RJ45 PoE ports)

### Product properties

Product type	Switch
Product family	Unmanaged PoE Switch 1000
Type	Stand-alone

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



MTTF	68 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
Basic functions	PSE, complies with IEEE 802.3at
Switch functions	
Basic functions	PSE, complies with IEEE 802.3at
Signal contact control voltage	24 V DC
Signal contact control current	100 mA
Status and diagnostic indicators	LEDs: $U_{S1}$ , $U_{S2}$ (redundant voltage supply), Alarm (alarm contact), Link/Activity and PoE per Ethernet port
Additional functions	Autonegotiation
Security functions	
Basic functions	PSE, complies with IEEE 802.3at
Electrical properties	
Power consumption	129 W
Local diagnostics	$U_{S1}$ , $U_{S2}$ Supply voltage Green LED PoE PoE detection Yellow LED LINK/ACT Link status/data transmission Green LED Alarm Power failure at $U_{S1}$ or $U_{S2}$ /Link failure
Maximum power dissipation for nominal condition	129.6 W
Test section	Supply voltage/functional ground 500 V AC 1 min
Transmission medium	Copper
Supply	
Supply voltage (DC)	24 V DC
Supply voltage range	18 V DC ... 57 V DC
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>
Inrush current	18 A (57 V DC for 100 $\mu$ s) 10 A (24 V DC for 100 $\mu$ s)
Residual ripple	3.6 $V_{PP}$ (within the permitted voltage range)
Max. current consumption	6.2 A (Maximum, nominal load)
Typical current consumption	148 mA (at $U_S$ = 24 V DC)
Function	
Signal contact control voltage	24 V DC
Signal contact control current	100 mA
Connection data	
Connection technology	
Connection name	Power supply
pluggable	yes
Power supply	
Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Conformance with EMC directives	IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion B
	IEC 61000-4-3 (immunity to radiated interference) Criterion A
	IEC 61000-4-4 (burst) Criterion B
	IEC 61000-4-5 (surge) Criterion B
	IEC 61000-4-6 (immunity to conducted interference) Criterion A
	IEC 61000-4-8 (immunity to magnetic fields) Criterion A
	EN 55022 (emitted interference) Criterion A

## System properties

Functionality	
Basic functions	PSE, complies with IEEE 802.3at

## Signaling

Status display	LEDs: U <sub>S1</sub> , U <sub>S2</sub> (redundant voltage supply), Alarm (alarm contact), Link/Activity and PoE per Ethernet port
----------------	--

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2891064>



**UL Listed**

Approval ID: E140324



**cUL Listed**

Approval ID: E140324



**KC**

Approval ID: MSIP-REI-PCK-2891064

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



## Classifications

### ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

### ETIM

ETIM 9.0	EC000734
----------	----------

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# FL SWITCH 1001T-4POE - Industrial Ethernet Switch

2891064

<https://www.phoenixcontact.com/us/products/2891064>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e0b0643d-cc19-4e3f-bf75-b46088fab890

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)