

UPS-BAT/LI-ION/24DC/120WH/KIT - Uninterruptible power supply replacement battery



2909830

<https://www.phoenixcontact.com/us/products/2909830>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Energy storage, LI-ION technology, 24 V DC, 120 Wh

Commercial data

Item number	2909830
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMUELY
GTIN	4055626388557
Weight per piece (including packing)	2,555 g
Weight per piece (excluding packing)	2,550 g
Country of origin	CN

UPS-BAT/LI-ION/24DC/120WH/KIT - Uninterruptible power supply replacement battery



2909830

<https://www.phoenixcontact.com/us/products/2909830>

Technical data

Input data

Input voltage	24 V DC
Buffer period	14 min (20 A)

Output data

Nominal output voltage	24 V DC
Output fuse	2x 25 A ATOF 32V
Connection in parallel	3
	3
Connection in series	no

Energy storage

End-of-charge voltage	28.5 V DC (20 °C)
Charging current	5 A
Nominal capacity	5 Ah
Latest startup date (battery only)	24 Months (20 °C ... 40 °C)
Battery technology	Lithium-Ion (LiFePO ₄)
Accumulator type	NEC ALM 12V7s HP
Size designation	Block
Battery pack	yes
IQ technology	Yes
Temperature sensor	yes
Suitable for fast charging	yes
Approved according to	UL Style 3321150 °C 600 V AC 750 V DC

Product properties

Product type	Battery module
Product family	Replacement battery
IQ technology	Yes

Insulation characteristics

Protection class	III
Degree of pollution	2

Dimensions

Width	130 mm
Height	100 mm
Depth	151 mm

Cable/line

UPS-BAT/LI-ION/24DC/120WH/KIT - Uninterruptible power supply replacement battery



2909830

<https://www.phoenixcontact.com/us/products/2909830>

Battery connecting cable: A+/-

Cable cross section	6 mm ²
Color	red/black

Battery connecting cable: B+/-

Cable cross section	6 mm ²
Color	red/black

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 65 °C
Max. permissible relative humidity (operation)	≤ 80 %

Ex data

Suited for EX-applications	no
----------------------------	----

UPS-BAT/LI-ION/24DC/120WH/KIT - Uninterruptible power supply replacement battery



2909830
<https://www.phoenixcontact.com/us/products/2909830>

Classifications

ETIM

ETIM 8.0	EC000357
----------	----------

UNSPSC

UNSPSC 21.0	26111700
-------------	----------

UPS-BAT/LI-ION/24DC/120WH/KIT - Uninterruptible power supply replacement battery



2909830

<https://www.phoenixcontact.com/us/products/2909830>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com