

**Siemens  
EcoTech**



circuit breaker frame size S00 for transformer protection with approval circuit breaker UL 489, CSA C22.2 no. 5-02 thermal overload release 5 A short-circuit release 104 A screw terminal standard switching capacity



|   |   |
|---|---|
| <b>product brand name</b>                                       | SIRIUS  |
| <b>product designation</b>                                      | Circuit breaker   |
| <b>design of the product</b>                                    | For transformer protection according to UL 489/CSA C22.2 No.5 |
| <b>product type designation</b>                                 | 3RV2  |
| <b>General technical data</b>                                   |   |
| <b>size of the circuit-breaker</b>                              | S00   |
| product extension auxiliary switch                              | Yes   |
| <b>power loss [W] for rated value of the current</b>            |   |
| • at AC in hot operating state                                  | 7.25 W  |
| • at AC in hot operating state per pole                         | 2.4 W   |
| insulation voltage with degree of pollution 3 at AC rated value | 690 V   |
| <b>surge voltage resistance rated value</b>                     | 6 kV  |
| <b>shock resistance according to IEC 60068-2-27</b>             | 25 g / 11 ms (rectangular impulse and sine pulse)             |
| <b>mechanical service life (operating cycles)</b>               |   |
| • of the main contacts typical                                  | 100 000   |
| • of auxiliary contacts typical                                 | 100 000   |
| electrical endurance (operating cycles) typical                 | 100 000   |
| <b>reference code according to IEC 81346-2</b>                  | Q   |
| <b>Substance Prohibitance (Date)</b>                            | 10/01/2009  |
| <b>Weight</b>   | 0.493 kg  |
| <b>Ambient conditions</b>                                       |   |
| installation altitude at height above sea level maximum         | 2 000 m   |
| <b>ambient temperature</b>                                      |   |
| • during operation  | -20 ... +60 °C  |
| • during storage  | -50 ... +80 °C  |
| • during transport  | -50 ... +80 °C  |
| relative humidity during operation                              | 10 ... 95 %   |
| <b>Environmental footprint</b>                                  |   |
| Environmental Product Declaration (EPD)                         | Yes   |
| global warming potential [CO2 eq] total                         | 74.698 kg   |
| global warming potential [CO2 eq] during manufacturing          | 1.98 kg   |
| global warming potential [CO2 eq] during sales                  | 0.134 kg  |
| global warming potential [CO2 eq] during operation              | 72.7 kg   |
| global warming potential [CO2 eq] after end of life             | -0.116 kg   |
| Siemens Eco Profile (SEP)                                       | Siemens EcoTech   |
| <b>Main circuit</b>   |   |
| <b>number of poles for main current circuit</b>                 | 3   |

|  |  |
|--|--|
| <b>type of voltage for main current circuit</b>  | AC   |
| <b>operating voltage</b>   |  |
| • rated value  | 20 ... 690 V   |
| • at AC-3 rated value maximum  | 690 V  |
| • at AC-3e rated value maximum   | 690 V  |
| <b>operating frequency rated value</b>   | 50 ... 60 Hz   |
| <b>operational current rated value</b>   | 5 A  |
| <b>operational current</b>   |  |
| • at AC-3 at 400 V rated value   | 5 A  |
| • at AC-3e at 400 V rated value  | 5 A  |
| <b>operating power</b>   |  |
| • at AC-3  |  |
| — at 230 V rated value   | 1.1 kW   |
| — at 400 V rated value   | 1.5 kW   |
| — at 500 V rated value   | 2.2 kW   |
| — at 690 V rated value   | 4 kW   |
| • at AC-3e   |  |
| — at 230 V rated value   | 1.1 kW   |
| — at 400 V rated value   | 1.5 kW   |
| — at 500 V rated value   | 2.2 kW   |
| — at 690 V rated value   | 4 kW   |
| <b>operating frequency</b>   |  |
| • at AC-3 maximum  | 15 1/h   |
| • at AC-3e maximum   | 15 1/h   |
| <b>Auxiliary circuit</b>   |  |
| <b>type of voltage for auxiliary and control circuit</b>                                       | AC/DC  |
| <b>number of NC contacts for auxiliary contacts</b>  | 0  |
| <b>number of NO contacts for auxiliary contacts</b>  | 0  |
| number of CO contacts for auxiliary contacts   | 0  |
| <b>Protective and monitoring functions</b>   |  |
| <b>product function</b>  |  |
| • ground fault detection   | No   |
| • phase failure detection  | No   |
| <b>design of the overload release</b>  | thermal  |
| <b>maximum short-circuit current breaking capacity (I<sub>cu</sub>)</b>                        |  |
| • at AC at 240 V rated value   | 100 kA   |
| • at AC at 400 V rated value   | 100 kA   |
| • at AC at 500 V rated value   | 100 kA   |
| • at AC at 690 V rated value   | 6 kA   |
| • at 480 AC Y/277 V according to UL 489 rated value  | 65 kA  |
| <b>operating short-circuit current breaking capacity (I<sub>cs</sub>) at AC</b>                |  |
| • at 240 V rated value   | 100 kA   |
| • at 400 V rated value   | 100 kA   |
| • at 500 V rated value   | 100 kA   |
| • at 690 V rated value   | 4 kA   |
| response value current of instantaneous short-circuit trip unit                                | 104 A  |
| <b>Short-circuit protection</b>  |  |
| <b>product function short circuit protection</b>   | Yes  |
| <b>design of the short-circuit trip</b>  | magnetic   |
| <b>design of the fuse link for IT network for short-circuit protection of the main circuit</b> |  |
| • at 400 V   | gG 32 A  |
| • at 500 V   | gG 32 A  |
| • at 690 V   | gG 25 A  |
| <b>Installation/ mounting/ dimensions</b>  |  |
| <b>mounting position</b>   | any  |
| <b>fastening method</b>  | screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 60715 |
| <b>height</b>  | 144 mm   |
| <b>width</b>   | 45 mm  |
| <b>depth</b>   | 97 mm  |
| <b>required spacing</b>  |  |

|  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• for grounded parts at 400 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— at the side</li> </ul> </li> <li>• for live parts at 400 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— at the side</li> </ul> </li> <li>• for grounded parts at 500 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— at the side</li> </ul> </li> <li>• for live parts at 500 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— at the side</li> </ul> </li> <li>• for grounded parts at 690 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— backwards</li> <li>— at the side</li> <li>— forwards</li> </ul> </li> <li>• for live parts at 690 V <ul style="list-style-type: none"> <li>— downwards</li> <li>— upwards</li> <li>— backwards</li> <li>— at the side</li> <li>— forwards</li> </ul> </li> </ul> | 30 mm<br>30 mm<br>30 mm<br><br>30 mm<br>30 mm<br>30 mm<br><br>30 mm<br>30 mm<br>30 mm<br><br>70 mm<br>70 mm<br>0 mm<br>30 mm<br>0 mm<br><br>70 mm<br>70 mm<br>0 mm<br>30 mm<br>0 mm |
| <b>Connections/ Terminals</b>  |   |
| <b>type of electrical connection</b>   |   |
| <ul style="list-style-type: none"> <li>• for main current circuit</li> </ul>   | screw-type terminals  |
| <b>arrangement of electrical connectors for main current circuit</b>   | Top and bottom  |
| <b>type of connectable conductor cross-sections</b>  |   |
| <ul style="list-style-type: none"> <li>• for main contacts <ul style="list-style-type: none"> <li>— solid or stranded</li> <li>— finely stranded with core end processing</li> </ul> </li> <li>• for AWG cables for main contacts</li> </ul>   | 1 ... 10 mm <sup>2</sup> , max. 2x 10 mm <sup>2</sup><br>1 ... 16 mm <sup>2</sup> , max. 6 + 16 mm <sup>2</sup><br>2x (14 ... 10)   |
| <b>tightening torque</b>   |   |
| <ul style="list-style-type: none"> <li>• for main contacts with screw-type terminals</li> </ul>  | 2.5 ... 3 N·m   |
| <b>design of screwdriver shaft</b>   | Diameter 5 to 6 mm  |
| <b>size of the screwdriver tip</b>   | Pozidriv size 2   |
| <b>design of the thread of the connection screw</b>  |   |
| <ul style="list-style-type: none"> <li>• for main contacts</li> </ul>  | M4  |
| <b>Safety related data</b>   |   |
| product function suitable for safety function  | Yes   |
| <b>suitability for use</b>   |   |
| <ul style="list-style-type: none"> <li>• safety-related switching on</li> <li>• safety-related switching OFF</li> </ul>  | No<br>Yes   |
| <b>service life maximum</b>  | 10 a  |
| <b>test wear-related service life necessary</b>  | Yes   |
| <b>proportion of dangerous failures</b>  |   |
| <ul style="list-style-type: none"> <li>• with low demand rate according to SN 31920</li> <li>• with high demand rate according to SN 31920</li> </ul>  | 40 %<br>50 %  |
| <b>B10 value with high demand rate according to SN 31920</b>   | 5 000   |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b>   | 50 FIT  |
| <b>ISO 13849</b>   |   |
| <b>device type according to ISO 13849-1</b>  | 3   |
| <b>overdimensioning according to ISO 13849-2 necessary</b>   | Yes   |
| <b>IEC 61508</b>   |   |

|   |  |
|---|--|
| safety device type according to IEC 61508-2   | Type A   |
| T1 value <ul style="list-style-type: none"> <li>for proof test interval or service life according to IEC 61508</li> </ul> | 10 a   |
| Electrical Safety   |  |
| protection class IP on the front according to IEC 60529   | IP20   |
| touch protection on the front according to IEC 60529  | finger-safe, for vertical contact from the front |
| Display   |  |
| display version for switching status  | Handle   |
| Approvals Certificates  |  |
| General Product Approval  |  |



KC



|                          |                   |                   |       |
|--------------------------|-------------------|-------------------|-------|
| General Product Approval | Test Certificates | Marine / Shipping | other |
|--------------------------|-------------------|-------------------|-------|

[BIS CRS](#)

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



[Miscellaneous](#)

|       |         |             |
|-------|---------|-------------|
| other | Railway | Environment |
|-------|---------|-------------|

[Confirmation](#)



[Special Test Certificate](#)



Siemens EcoTech



[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2811-1FD10>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2811-1FD10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2811-1FD10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)




[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV2811-1FD10&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2811-1FD10&lang=en)

Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2811-1FD10/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2811-1FD10&objecttype=14&gridview=view1>





last modified:

5/1/2025