

Siemens
EcoTech



RONIS key-operated switch, 22 mm, round, plastic, lock number SB30, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, key removal O+I, possible special locks: SB31, 421, 455 Z=50-unit packaging



product brand name	SIRIUS ACT
product designation	Key-operated switches
design of the product	Actuating/signaling element
product type designation	3SU1
product line	Plastic, black, 22 mm
manufacturer's article number of included key	3SU1950-0FB80-0AA0
Actuator	
principle of operation of the actuating element	latching, 90° (10:30 h/13:30 h)
product extension optional light source	No
color	
• of the actuating element	silver
material of the actuating element	metal
shape of the actuating element	Key
outer diameter of the actuating element	29.5 mm
number of switching positions	2
switch position for key distraction	O+I
actuating angle	
• clockwise	90°
lock make	RONIS
key number	SB30
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	plastic
color of the front ring	black
General technical data	
protection class IP	IP66, IP67, IP69(IP69K)
protection class IP of the terminal	IP20
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12, 13
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating frequency maximum	1 800 1/h
mechanical service life (operating cycles) typical	1 000 000

reference code according to IEC 81346-2	S				
Substance Prohibittance (Date)	10/01/2014				
Weight	56 g				
Ambient conditions					
ambient temperature					
• during operation	-25 ... +70 °C				
• during storage	-40 ... +80 °C				
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)				
Environmental footprint					
Environmental Product Declaration (EPD)	Yes				
global warming potential [CO2 eq] total	0.787 kg				
global warming potential [CO2 eq] during manufacturing	0.566 kg				
global warming potential [CO2 eq] during operation	0.235 kg				
global warming potential [CO2 eq] after end of life	-0.015 kg				
Siemens Eco Profile (SEP)	Siemens EcoTech				
Installation/ mounting/ dimensions					
height	29.5 mm				
width	29.5 mm				
shape of the installation opening	round				
mounting diameter	22.3 mm				
positive tolerance of installation diameter	0.4 mm				
mounting height	49.4 mm				
installation width	29.5 mm				
installation depth	25.4 mm				
Approvals Certificates					
<table border="1"> <thead> <tr> <th>General Product Approval</th> <th>Test Certificates</th> </tr> </thead> <tbody> <tr> <td>     </td> <td> Type Test Certificates/Test Report Special Test Certificate </td> </tr> </tbody> </table>		General Product Approval	Test Certificates	   	Type Test Certificates/Test Report Special Test Certificate
General Product Approval	Test Certificates				
   	Type Test Certificates/Test Report Special Test Certificate				

other	Environment
-------	-------------

[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1000-4BF11-0AA0-Z X90>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1000-4BF11-0AA0-Z X90>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1000-4BF11-0AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1000-4BF11-0AA0-Z X90&lang=en



last modified:

4/1/2025 