

Siemens  
EcoTech



Siemens keyswitch, C, 22 mm, round, metal, shiny, lock number LSG1, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, key removal O+I, Z=50-unit packaging



|                                                    |                                    |
|----------------------------------------------------|------------------------------------|
| product brand name                                 | SIRIUS ACT                         |
| product designation                                | Key-operated switches              |
| design of the product                              | Actuating/signaling element        |
| product type designation                           | 3SU1                               |
| product line                                       | Metal, shiny, 22 mm                |
| manufacturer's article number of included key      | <a href="#">3SU1950-0FN80-0AA0</a> |
| <b>Actuator</b>                                    |                                    |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)    |
| product extension optional light source            | No                                 |
| color                                              |                                    |
| • of the actuating element                         | silver                             |
| material of the actuating element                  | metal                              |
| shape of the actuating element                     | Key                                |
| outer diameter of the actuating element            | 29.5 mm                            |
| number of switching positions                      | 2                                  |
| switch position for key distraction                | O+I                                |
| actuating angle                                    |                                    |
| • clockwise                                        | 90°                                |
| lock make                                          | Siemens, C                         |
| key number                                         | LSG1                               |
| <b>Front ring</b>                                  |                                    |
| product component front ring                       | Yes                                |
| design of the front ring                           | Standard                           |
| material of the front ring                         | Metal, high gloss                  |
| color of the front ring                            | silver                             |
| <b>General technical data</b>                      |                                    |
| protection class IP                                | IP66, IP67, IP69(IP69K)            |
| protection class IP of the terminal                | IP20                               |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13         |
| shock resistance                                   |                                    |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms   |
| vibration resistance                               |                                    |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                  |
| operating frequency maximum                        | 1 800 1/h                          |
| mechanical service life (operating cycles) typical | 300 000                            |
| reference code according to IEC 81346-2            | S                                  |
| Substance Prohibitance (Date)                      | 10/01/2014                         |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>SVHC substance name</b>                                     | Lead - 7439-92-1                                                   |
| <b>Weight</b>                                                  | 0.147 kg                                                           |
| <b>Ambient conditions</b>                                      |                                                                    |
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| <b>Environmental footprint</b>                                 |                                                                    |
| Environmental Product Declaration (EPD)                        | Yes                                                                |
| global warming potential [CO2 eq] total                        | 0.593 kg                                                           |
| global warming potential [CO2 eq] during manufacturing         | 0.625 kg                                                           |
| global warming potential [CO2 eq] during operation             | 0.235 kg                                                           |
| global warming potential [CO2 eq] after end of life            | -0.267 kg                                                          |
| Siemens Eco Profile (SEP)                                      | Siemens EcoTech                                                    |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                    |
| <b>height</b>                                                  | 29.5 mm                                                            |
| <b>width</b>                                                   | 29.5 mm                                                            |
| <b>shape of the installation opening</b>                       | round                                                              |
| <b>mounting diameter</b>                                       | 22.3 mm                                                            |
| <b>positive tolerance of installation diameter</b>             | 0.4 mm                                                             |
| <b>mounting height</b>                                         | 61 mm                                                              |
| <b>installation width</b>                                      | 29.5 mm                                                            |
| <b>installation depth</b>                                      | 25.4 mm                                                            |
| <b>Approvals Certificates</b>                                  |                                                                    |
| <b>General Product Approval</b>                                | <b>Test Certificates</b>                                           |



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other

Environment

[Confirmation](#)



Siemens  
EcoTech



[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-5HF11-0AA0-Z X90>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-5HF11-0AA0-Z X90>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-5HF11-0AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-5HF11-0AA0-Z X90&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-5HF11-0AA0-Z X90&lang=en)



last modified:

4/1/2025 