

Siemens  
EcoTech



Indicator lights, 22 mm, round, plastic, yellow, lens, smooth, with holder, LED module, with integrated LED 230 V AC, spring-type terminal, Z=20-unit packaging



|                                                  |                                    |
|--------------------------------------------------|------------------------------------|
| product brand name                               | SIRIUS ACT                         |
| product designation                              | Indicator lights                   |
| design of the product                            | Complete unit                      |
| product type designation                         | 3SU1                               |
| product line                                     | Plastic, black, 22 mm              |
| manufacturer's article number                    |                                    |
| • of supplied LED module                         | <a href="#">3SU1401-1BF30-3AA0</a> |
| • of the supplied holder                         | <a href="#">3SU1550-0AA10-0AA0</a> |
| • of supplied repeater                           | <a href="#">3SU1001-6AA30-0AA0</a> |
| <b>Enclosure</b>                                 |                                    |
| number of command points                         | 1                                  |
| <b>Actuator</b>                                  |                                    |
| product extension optional light source          | Yes                                |
| color                                            |                                    |
| • of the actuating element                       | yellow                             |
| material of the actuating element                | plastic                            |
| shape of the actuating element                   | round                              |
| outer diameter of the actuating element          | 29.45 mm                           |
| <b>Front ring</b>                                |                                    |
| product component front ring                     | No                                 |
| <b>Holder</b>                                    |                                    |
| material of the holder                           | Plastic                            |
| <b>Display</b>                                   |                                    |
| number of LED modules                            | 1                                  |
| <b>General technical data</b>                    |                                    |
| product component light source                   | Yes                                |
| insulation voltage rated value                   | 320 V                              |
| degree of pollution                              | 3                                  |
| surge voltage resistance rated value             | 4 kV                               |
| protection class IP                              | IP66, IP67, IP69(IP69K)            |
| protection class IP of the terminal              | IP20                               |
| degree of protection NEMA rating                 | 1, 2, 3, 3R, 4, 4X, 12, 13         |
| shock resistance                                 |                                    |
| • according to IEC 60068-2-27                    | sinusoidal half-wave 15g / 11 ms   |
| • for railway applications according to EN 61373 | Category 1, Class B                |
| vibration resistance                             |                                    |
| • according to IEC 60068-2-6                     | 10 ... 500 Hz: 5g                  |

|                                                                |                                                                                                                                                                                                                                                                                                                             |                   |       |
|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-------|
| • for railway applications according to EN 61373               | Category 1, Class B                                                                                                                                                                                                                                                                                                         |                   |       |
| reference code according to IEC 81346-2                        | P                                                                                                                                                                                                                                                                                                                           |                   |       |
| Substance Prohibitance (Date)                                  | 10/01/2014                                                                                                                                                                                                                                                                                                                  |                   |       |
| SVHC substance name                                            | Lead monoxide (lead oxide) - 1317-36-8<br>2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5                                                                                                                                                                                                             |                   |       |
| Weight                                                         | 0.054 kg                                                                                                                                                                                                                                                                                                                    |                   |       |
| Supply voltage                                                 |                                                                                                                                                                                                                                                                                                                             |                   |       |
| type of voltage of the supply voltage of the light source      | AC                                                                                                                                                                                                                                                                                                                          |                   |       |
| supply voltage of the light source at AC                       | <div><div>• at 50 Hz rated value</div><div>230 V</div><div>• at 60 Hz rated value</div><div>230 V</div><div>• at 60 Hz rated value</div><div>230 ... 230 V</div></div>                                                                                                                                                      |                   |       |
| relative negative tolerance of the supply voltage              | 20 %                                                                                                                                                                                                                                                                                                                        |                   |       |
| relative positive tolerance of the supply voltage              | 20 %                                                                                                                                                                                                                                                                                                                        |                   |       |
| Control circuit/ Control                                       |                                                                                                                                                                                                                                                                                                                             |                   |       |
| inrush current maximum                                         | 3 A                                                                                                                                                                                                                                                                                                                         |                   |       |
| Connections/ Terminals                                         |                                                                                                                                                                                                                                                                                                                             |                   |       |
| type of electrical connection                                  | other                                                                                                                                                                                                                                                                                                                       |                   |       |
| • of modules and accessories                                   | Spring-type terminal                                                                                                                                                                                                                                                                                                        |                   |       |
| type of connectable conductor cross-sections                   | <div><div>• solid without core end processing</div><div>2x (0.25 ... 1.5 mm²)</div><div>• finely stranded with core end processing</div><div>2x (0.25 ... 0.75 mm²)</div><div>• finely stranded without core end processing</div><div>2x (0.25 ... 1.5 mm²)</div><div>• for AWG cables</div><div>2x (24 ... 16)</div></div> |                   |       |
| tightening torque of the screws in the bracket                 | 1 ... 1.2 N·m                                                                                                                                                                                                                                                                                                               |                   |       |
| Lamp                                                           |                                                                                                                                                                                                                                                                                                                             |                   |       |
| type of light source                                           | LED                                                                                                                                                                                                                                                                                                                         |                   |       |
| color of the light source                                      | yellow                                                                                                                                                                                                                                                                                                                      |                   |       |
| light intensity                                                | 900 ... 1 400 mcd                                                                                                                                                                                                                                                                                                           |                   |       |
| Ambient conditions                                             |                                                                                                                                                                                                                                                                                                                             |                   |       |
| ambient temperature                                            | <div><div>• during operation</div><div>-25 ... +70 °C</div><div>• during storage</div><div>-40 ... +80 °C</div></div>                                                                                                                                                                                                       |                   |       |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel)                                                                                                                                                                                    |                   |       |
| Environmental footprint                                        |                                                                                                                                                                                                                                                                                                                             |                   |       |
| Environmental Product Declaration(EPD)                         | Yes                                                                                                                                                                                                                                                                                                                         |                   |       |
| global warming potential [CO2 eq] total                        | 0.787 kg                                                                                                                                                                                                                                                                                                                    |                   |       |
| global warming potential [CO2 eq] during manufacturing         | 0.566 kg                                                                                                                                                                                                                                                                                                                    |                   |       |
| global warming potential [CO2 eq] during operation             | 0.235 kg                                                                                                                                                                                                                                                                                                                    |                   |       |
| global warming potential [CO2 eq] after end of life            | -0.015 kg                                                                                                                                                                                                                                                                                                                   |                   |       |
| Siemens Eco Profile (SEP)                                      | Siemens EcoTech                                                                                                                                                                                                                                                                                                             |                   |       |
| Installation/ mounting/ dimensions                             |                                                                                                                                                                                                                                                                                                                             |                   |       |
| fastening method                                               | front plate mounting                                                                                                                                                                                                                                                                                                        |                   |       |
| • of modules and accessories                                   | Front plate mounting                                                                                                                                                                                                                                                                                                        |                   |       |
| height                                                         | 40 mm                                                                                                                                                                                                                                                                                                                       |                   |       |
| width                                                          | 30 mm                                                                                                                                                                                                                                                                                                                       |                   |       |
| shape of the installation opening                              | round                                                                                                                                                                                                                                                                                                                       |                   |       |
| mounting diameter                                              | 22.3 mm                                                                                                                                                                                                                                                                                                                     |                   |       |
| positive tolerance of installation diameter                    | 0.4 mm                                                                                                                                                                                                                                                                                                                      |                   |       |
| mounting height                                                | 11.8 mm                                                                                                                                                                                                                                                                                                                     |                   |       |
| installation width                                             | 29.5 mm                                                                                                                                                                                                                                                                                                                     |                   |       |
| installation depth                                             | 49.7 mm                                                                                                                                                                                                                                                                                                                     |                   |       |
| Approvals Certificates                                         |                                                                                                                                                                                                                                                                                                                             |                   |       |
| General Product Approval                                       |                                                                                                                                                                                                                                                                                                                             | Test Certificates | other |



[Type Test Certificates/Test Report](#)

[Confirmation](#)



Siemens  
EcoTech



[Environmental Con-  
firmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1106-6AA30-3AA0-Z X90>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1106-6AA30-3AA0-Z X90>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1106-6AA30-3AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1106-6AA30-3AA0-Z X90&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1106-6AA30-3AA0-Z X90&lang=en)





last modified:

4/2/2025 