

TECHNICAL DATA

Fluke 301D AC/DC Clamp Meter



Key features

- The body weighs only 154g and is 16mm thick, which is light and portable and can be put into a pocket
- The slim and thin jaw of only 10mm can easily fit into tightly packed wires
- 600A AC/DC range (D model), 0.01A high resolution
- Tests voltage, resistance and continuity
- Tests current frequency and voltage frequency
- Tests capacitance and diodes
- Backlight

Product overview: Fluke 301D AC/DC Clamp Meter

The Fluke 301D Series AC/DC Clamp Meter is designed with a lightweight and compact body, which allows you to carry it around in your pocket. The slim and thin jaw can easily fit into tightly packed wires. The Fluke 301D test current, voltage, resistance, continuity, frequency (voltage and current), capacitance, and diode, etc.. You can handle multiple test needs with just one tool. With the AC/DC function, it can be applied to more application scenarios requiring DC testing, such as new energy of PV and wind power, new energy vehicles, communications, data centers, etc..

Specifications: Fluke 301D AC/DC Clamp Meter

Ordering information



FLUKE-301D/ESP

Fluke 301D Blade Series AC/DC Clamp Meter

Includes:

- Fluke 301D Clamp Meter
 - TL75 test lead
 - (2) AAA batteries
-



Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2025 Fluke Corporation.
Specifications subject to change without notice.
06/2025

**Modification of this document is not permitted
without written permission from Fluke
Corporation.**