

48-Port Serial Console Server, USB Ports (2) - Dual GbE NIC, 4 Gb Flash, Desktop/1U Rack, CE, TAA

MODEL NUMBER: B097-048-INT



48-port serial console server lets you remotely access and control serial-based networking equipment through one highly secure gateway.

Features

Securely Access All Your Serial and Network Devices from Anywhere in the World at Any Time This USB console server provides secure in-band (primary network) and optional out-of-band (alternate channel) remote access to serial- and network-connected routers, network switches, firewalls, PBX systems, UPS systems, PDUs and other devices. It offers reliable network connectivity with dual Gigabit primary and failover Ethernet ports and dual power supplies. You can use it in a wide variety of applications, including wiring closets, branch offices, kiosks, point-of-sale and other remote sites where a quick identification and resolution of network issues is imperative.

Simple and Flexible Accessibility with Industry-Standard Integration The 48 RJ45 console ports are configured to use standard Cat5e/6 patch cable when connecting to Cisco devices. They integrate with industry-standard directory servers using TACACS+, RADIUS, LDAP and Kerberos authentication. Provides 4 Gb of internal NAND flash memory, which can be used for log storage and file storage.

Connect an External Modem for Optional Out-of-Band Access Connect one of the 48 RJ45 ports to an external Multitech MT9234MU-CDC-XR or US Robotics USR5637 USB modem (not included) to receive out-of-band (alternate channel) access when remote sites experience a network outage.

Gateway Ports Forward to Routers and Other Hosts Each gateway can port forward to an unlimited number of locally networked hosts (computers, routers). This rack console also includes a built-in stateful firewall and embedded DHCP server to host a separate management LAN for critical traffic.

The Utmost in Security to Keep Your Sensitive Data Private The console server supports the following security features and standards: PCI DSS 3.2, FIPS 140-2, SSL and SSH, stateful firewall, OpenVPN and IPSec VPN support. The embedded FIPS 140-2 OpenSSL cryptographic module is validated to meet FIPS 140-2 standards and has received Certificate #2473.

PowerMan PDU and Network UPS Tools for Enhanced Monitoring and Control This 48-port serial console server uses PowerMan for PDU and RPC management and Network UPS Tools for UPS system monitoring and management. It provides support for a range of power products, so you can remotely manage power to your connected equipment.

USB Console Connects to PDUs and UPS Systems Two USB 2.0 console ports allow connection to

Highlights

- Manage routers, UPS systems and other serial-based equipment from anywhere 24/7
- Validated to meet FIPS 140-2 standards to ensure utmost protection of private data
- Dual Gigabit Ethernet ports for primary network connection and automatic failover
- Designed for standard Cat5e/6 patch cable when connecting to Cisco devices
- CE-marked to ensure compliance with EEA (European Economic Area) standards

Applications

- Securely access (in-band) and control servers, routers, KVM switches and other serial-connected devices in your data center 24/7
- Manage diverse server and device platforms using a network connection
- Diagnose and fix issues with your IT infrastructure remotely with little or no downtime
- Troubleshoot equipment issues without spending time/money traveling to remote locations

Package Includes

- B097-048-INT 48-Port Serial Console Server
- (2) Cat5e patch cables, 6 ft.
- Straight-through serial adapter, DB9 to RJ45 (F/F)
- Crossover serial adapter, DB9 to RJ45 (F/F)
- Modular serial adapter, DB9 to RJ45 (M/F)
- Rack-mounting hardware
- (6) Rubber feet
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

newer devices with USB console ports, such as a wide variety of PDUs and UPS systems with WEBCARDLX or other LX Platform remote management cards.

Compact Design for Convenient MountingThe heavy-duty steel housing comes with mounting brackets for 1U installation in an EIA-standard 19-inch rack. Its fanless form factor also allows desktop deployment on included rubber feet that help prevent the unit from sliding. User-supplied power cords connect the console server to a compatible power source.

TAA-Compliant and CE-MarkedThe B097-048-INT is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts. It is also CE-marked in compliance with EEA standards.

Specifications

OVERVIEW	
UPC Code	037332241443
Multi-User	Yes
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Voltage Compatibility (VDC)	N/A
Power Input Receptacle	IEC-320-C14
Redundancy - Dual Power Inputs	Yes
POWER	
Power Consumption (Watts)	25
CONNECTIONS	
Number of Ports	48
Side A - Connector 1	RJ45 (FEMALE)
Side A - Connector 2	(2) USB A (FEMALE)
Side B - Connector 1	(48) RJ45 (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	8 LED's for Power, Heartbeat-Firmware Running, Serial Connectivity and Network Ports
PHYSICAL	
Color	Black
Material of Construction	Metal
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	3.30 x 10.60 x 19.30



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	8.38 x 26.92 x 49.02
Shipping Weight (lbs.)	7.60
Shipping Weight (kg)	3.45
Unit Dimensions (hwd / in.)	1.750 x 6.900 x 17.320
Unit Dimensions (hwd / cm)	4.5 x 17.5 x 44
Unit Packaging Type	Box
Unit Weight (lbs.)	7
Unit Weight (kg)	3.18
ENVIRONMENTAL	
Operating Temperature Range	41° to 122°F (5° to 50°C)
Storage Temperature Range	-22° to 140°F (-30° to 60°C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	85.3 BTU/Hr
COMMUNICATIONS	
IP Remote Access	Yes
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3ab; 802.3ad
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Port Selection	CLI; GUI
Driver Required	No
Authentication Supported	RADIUS; LDAP; TACACS
Common Access Card (CAC) Support	No
REMOTE ACCESS	
Modem Port	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	4-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.