

#### Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

## Heavy-Duty PDU Power Cord, Locking C13 to C14 - 15A, 250V, 14 AWG, 10 ft. (3.05 m)

MODEL NUMBER: P005-L10



C14 to C13 power cable ensures a secure connection for all your equipment. Locking C13 connector prevents accidental disconnection.

#### Features

**Locking C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 power cable can be used to power a computer, printer or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 10 feet.

**Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The P005-L10's locking C13 connector protects your critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Tough Heavy-Duty Cable is Ideal for Server Applications** The 10-foot cord can be used to power equipment that requires a higher-rated heavy-duty cable, such as servers, routers, network switches and blade server enclosures.

**Lifetime Limited Warranty** C13 to C14 PDU-style extension cord is backed by a lifetime limited warranty, ensuring reliability and performance.

#### Highlights

- Securely connect network devices such as servers and routers to an AC outlet
- Locking C13 connector prevents accidental disconnection
- 10-ft. (3.05 m) heavy-duty cord provides power in server applications
- Adds 10-ft. (3.05 m) to your existing power connection for more flexibility when placing devices
- C13-to-C14 extension cord is ideal replacement for worn-out or missing cable

#### Applications

- Connect devices like computers, servers and monitors to a PDU up to 10-ft. (3.05 m) away in your data center
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

#### Package Includes

- P005-L10 Heavy-Duty Locking Power Extension Cord - PC Style Male (IEC-320-C14) to Locking PC Style Female (IEC-320-C13), 10-ft. (3.05 m)

## Specifications

OVERVIEW	
UPC Code	037332218100
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU



Powering Business Worldwide

TRIPP LITE  
SERIES

Country/Region	Global
<b>INPUT</b>	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13 - LOCKING
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 9.25 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 23.50 x 1.27
Shipping Weight (lbs.)	1.06
Shipping Weight (kg)	0.48
Unit Dimensions (hwd / in.)	12.800 x 9.250 x 0.500
Unit Weight (lbs.)	1.0600
Unit Weight (kg)	0.48
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No



Powering Business Worldwide

TRIPP LITE  
SERIES

Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.