




REV.	DATE	ECR NO.	DESCRIPTION
NC	02/06/03	XXXXX	INITIAL RELEASE
A	12/20/12	2416	UPDATE DRAWING FORMAT



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: DC-12.4 GHz
3. VSWR (RETURN LOSS): 1.3 MAX.
4. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS MIN.
5. DURABILITY: 500 CYCLES MIN.
6. TEMPERATURE RANGE: -65°C TO +165°C
7. THE CONTACT PIN MUST WITHSTAND A 6 LBS. MIN. AXIAL FORCE AND 4 IN-OZ ROTATIONAL TORQUE.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING		<table><tr><td colspan="2">APPROVALS</td><td>DATE</td></tr><tr><td>DRAWN</td><td>M.ZHANG</td><td>12/20/12</td></tr><tr><td>CHECKED</td><td></td><td></td></tr><tr><td>ISSUED</td><td></td><td></td></tr><tr><td>SHEET</td><td>1 OF 1</td><td></td></tr></table>		APPROVALS		DATE	DRAWN	M.ZHANG	12/20/12	CHECKED			ISSUED			SHEET	1 OF 1		Amphenol Connex			
APPROVALS		DATE																									
DRAWN	M.ZHANG	12/20/12																									
CHECKED																											
ISSUED																											
SHEET	1 OF 1																										
<table><tr><td colspan="5">PART DESCRIPTION</td></tr><tr><td colspan="5">SMA FOUR (4) HOLE PANEL RECEPTACLE JACK EXTEND TEFLON (.145"/.295")</td></tr></table>					PART DESCRIPTION					SMA FOUR (4) HOLE PANEL RECEPTACLE JACK EXTEND TEFLON (.145"/.295")																	
PART DESCRIPTION																											
SMA FOUR (4) HOLE PANEL RECEPTACLE JACK EXTEND TEFLON (.145"/.295")																											
<table><tr><td colspan="2">PART NO.</td><td colspan="3">132146–32</td></tr></table>					PART NO.		132146–32																				
PART NO.		132146–32																									
<table><tr><td>DWG. NO.</td><td>132146–32.DWG</td><td>REV.</td><td>A</td><td>SIZE</td><td>A</td><td>SCALE</td><td>NA</td></tr></table>					DWG. NO.	132146–32.DWG	REV.	A	SIZE	A	SCALE	NA															
DWG. NO.	132146–32.DWG	REV.	A	SIZE	A	SCALE	NA																				
<table><tr><td>3</td><td>CONTACT PIN</td><td>BER. COPPER</td><td>GOLD</td><td>1</td></tr><tr><td>2</td><td>INSULATOR</td><td>PTFE</td><td>NATURAL</td><td>1</td></tr><tr><td>1</td><td>BODY</td><td>BRASS</td><td>GOLD</td><td>1</td></tr></table>		3	CONTACT PIN	BER. COPPER	GOLD	1	2	INSULATOR	PTFE	NATURAL	1	1	BODY	BRASS	GOLD	1	<table><tr><td>DESCRIPTION</td><td>MATERIAL</td><td>FINISH</td><td>QTY</td></tr></table>		DESCRIPTION	MATERIAL	FINISH	QTY					
3	CONTACT PIN	BER. COPPER	GOLD	1																							
2	INSULATOR	PTFE	NATURAL	1																							
1	BODY	BRASS	GOLD	1																							
DESCRIPTION	MATERIAL	FINISH	QTY																								