



SIMATIC ET 200SP, ANALOG INPUT MODULE, AI 4XU/I 2-WIRE STANDARD, PACKING UNIT: 10 PIECES, FITS TO BU-TYPE A0, A1, COLOR CODE CC03, MODULE DIAGNOSIS, 16BIT, +/-0,3%

General information	
Product type designation	AI 4x U/I 2-wire
HW functional status	From FS02
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC03
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14 / -
• STEP 7 configurable/integrated from version	V5.6 and higher
• PCS 7 configurable/integrated from version	V8.1 SP1
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	37 mA; without sensor supply
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	20 mA; max. 50 mA per channel for a duration < 10 s
Power loss	
Power loss, typ.	0.85 W; Without encoder supply voltage
Address area	
Address space per module	
• Address space per module, max.	8 byte; + 1 byte for QI information

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0, A1
Analog inputs	
Number of analog inputs	4; Differential inputs
permissible input voltage for voltage input (destruction limit), max.	30 V
permissible input current for current input (destruction limit), max.	50 mA
Cycle time (all channels), min.	Sum of the basic conversion times and additional processing times (depending on the parameterization of the active channels)
Input ranges (rated values), voltages	
• 0 to +10 V	Yes; 15 bit
— Input resistance (0 to 10 V)	120 kΩ
• 1 V to 5 V	Yes; 15 bit
— Input resistance (1 V to 5 V)	120 kΩ
• -10 V to +10 V	Yes; 16 bit incl. sign
— Input resistance (-10 V to +10 V)	120 kΩ
• -5 V to +5 V	Yes; 16 bit incl. sign
— Input resistance (-5 V to +5 V)	120 kΩ
Input ranges (rated values), currents	
• 0 to 20 mA	Yes; 15 bit
— Input resistance (0 to 20 mA)	100 Ω; + approx. 0.7 V diode forward voltage
• 4 mA to 20 mA	Yes; 15 bit
— Input resistance (4 mA to 20 mA)	100 Ω; + approx. 0.7 V diode forward voltage
Cable length	
• shielded, max.	1 000 m; 200 m for voltage measurement
Analog value generation for the inputs	
Measurement principle	integrating (Sigma-Delta)
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Interference voltage suppression for interference frequency f1 in Hz	16.6 / 50 / 60 Hz
• Conversion time (per channel)	180 / 60 / 50 ms
Smoothing of measured values	
• Number of smoothing levels	4; None; 4/8/16 times
• parameterizable	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
• for current measurement as 2-wire transducer	Yes
— Burden of 2-wire transmitter, max.	650 Ω
• for current measurement as 4-wire transducer	No
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.5 %
• Current, relative to input range, (+/-)	0.5 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input range, (+/-)	0.3 %
• Current, relative to input range, (+/-)	0.3 %
Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB

• Common mode voltage, max.	10 V
• Common mode interference, min.	90 dB
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	No
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; at 4 to 20 mA
• Short-circuit	Yes; with 1 to 5 V or 2-wire mode: Short-circuit of the encoder supply to ground or of an input to the encoder supply
• Group error	Yes
• Overflow/underflow	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green LED
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red LED
Potential separation	
Potential separation channels	
• between the channels	Yes; channel group-specific between 2-wire current input group and voltage input group
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes; only for voltage inputs
Permissible potential difference	
between the inputs (UCM)	10 V DC
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for applications according to AMS 2750	Yes; Declaration of Conformity, see online support entry 109757262
Suitable for applications according to CQI-9	Yes
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C; < 0 °C as of FS02
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C; < 0 °C as of FS02
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Dimensions	
Width	15 mm
Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	31 g
Classifications	

	Version	Classification
eClass	14	27-24-26-01
eClass	12	27-24-26-01
eClass	9.1	27-24-26-01
eClass	9	27-24-26-01
eClass	8	27-24-26-01
eClass	7.1	27-24-26-01
eClass	6	27-24-26-01
ETIM	9	EC001596
ETIM	8	EC001596
ETIM	7	EC001596

IDEA	4	3562
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



EG-Konf.



[Manufacturer Declaration](#)

[Miscellaneous](#)

[Metrological Approval](#)



RCM

Maritime application

Environment



RMRS



last modified:

5/22/2024