



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		3/DEC/2013	
A1	ADDED 1 FT LENGTH		12/SEP/2017	
A2	Added ACD PIN to the table		08/Oct/2019	



LENGTH	CUSTOMER P/N
1FT(305±20mm)	CO-058SMAMMRP-001
3FT(914±30mm)	CO-058SMAMMRP-003
6FT(1829±40mm)	CO-058SMAMMRP-006
10FT(3048±40mm)	CO-058SMAMMRP-010
15FT(4572±50mm)	CO-058SMAMMRP-015
25FT(7620±100mm)	CO-058SMAMMRP-025



NOTES:

- 1.CABLE:120AWG(19/0.18±0.008mm)*1C+AL/MYLAR +BRAID(16*8/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 2.95±0.10mm COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC; OD=Ø5.0±0.15mm COLOR:UL813 BLACK
- MARKING:RG58C/U COAXIAL CABLE 50 OHM ROHS
- 2.CONNECTOR:Reverse Polarity SMA Male GOLD-PPLATING
- 3.OPEN/SHORT MISS WIRE TEST 100%
- 4.CONDUCTOR RESISTANCE $\leq 36.7\Omega/\text{km}$
- 5.INSULATION RESISTANCE $\geq 2M\Omega$ DC300V 0.01Sec

ALL MATERIALS SHALL ACCORD WITH ROHS STANDARD.

SECTION A-A

PIN OUT:	
CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:	E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDCOTT, NY 13760	
	DECIMALS	ANGLES		
	X ±X	±X°		
THIRD ANGLE PROJECTION	.XX ±.XX	CHECKED	LF	3/DEC/2013
	.XXX ±.XXX	BA	3/DEC/2013	
		RESP ENG		
MFG ENG		SIZE DWG. NO.		
		A CO-058SMAMMRP-XXX		
REV.		A2		

NOTES: UNLESS OTHERWISE SPECIFIED