




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR ENCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		06/Aug/09	
A1	ADD LENGTH-6"		19/Oct/2016	
A2	ADD LENGTH: 1.5FT & 2.5FT		25/Mar/2022	



SMA MALE RA



SMA MALE RA

SECTION A-A

NOTES:

1. CABLE:[26AWG(7/0.17mm)*1C+BRAID(16*5/0.10mm)]
INSULATION:FEP(Teflon) OD= 1.5±0.05mm ;COLOR:NATURAL
JACKET:FEP(Teflon) ;OD=Ø2.54±0.10mm
COLOR:BROWN TRANSPARENT.
(The outer jacket operating temperature can be 200 degree C)
MARKING:RG316/U COAXIAL CABLE 50 OHM RoHS
 - 2.CONNECTOR:SMA Male RA GOLD-PLATING
 - 3.OPEN/SHORT MISS WIRE TEST 100%
 - 4.CONDUCTOR RESISTANCE $\leq$ 375 Ω /km
 - 5.INSULATION RESISTANCE $\geq$ 2M Ω DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

LENGTH & P/N Table

LENGTH	P/N
6"(152±15mm)	CO-316RASMXX2-006IN
1FT(305±20mm)	CO-316RASMXX2-001
1.5FT(457±20mm)	CO-316RASMXX2-001.5
2FT(610±30mm)	CO-316RASMXX2-002
2.5FT(762±30mm)	CO-316RASMXX2-002.5
3FT(914±30mm)	CO-316RASMXX2-003
4FT(1219±30mm)	CO-316RASMXX2-004
5FT(1524±30mm)	CO-316RASMXX2-005
7.5FT(2286±40mm)	CO-316RASMXX2-007.5
10FT(3048±40mm)	CO-316RASMXX2-010

PIN OUT:

CENTER	CENTER
SHELL	SHELL



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DECIMALS		APPROVALS	DATE		
X	±X	LF	18/Oct/2016		
XX	±XX	CHECKED	BA		
XXX	±XXX	RESP ENG			
THIRD ANGLE PROJECTION		REF ENG			
		MFG ENG			
ISO FILE:		SIZE	DWG. NO.	CO-316RASMXX2-XXX	REV. A2

NOTES: UNLESS OTHERWISE SPECIFIED

4

3

2

1