





△ N = Number of poles
DimL=N×5.00±1.5
DimB=(N-1)×5.00

POLES	Dim L	Dim B
1p	±0.1	±0.15
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△	1/31'07	The soldering temperature from 245° to 250°	Aaron
△	05/28'13	change the structure	Da cheng
△	05/28'13	update the drawing	Da cheng
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Insulator body: Thermoplastic (UL94V-0)
- Item ② Insulating cover :Thermoplastic (UL94V-0)
- Item ③ Contact pin : Brass.Tin plated
- Item ④ Wire guard: Stainless steel

Electrical:

cULus

- Voltage rating: 250V

- Current rating: 8A

- Wire range:

- Solid wire(AWG): 12-28

- Stranded wire(AWG): 12-28

- Wire strip length: 8-9mm

- Withstanding Voltage: 15KV

- Operating temperature: -40°C to +115°C

- △△ Soldering temperature: 260°C±5°C/5 Sec

- Safety Approval: cULus

- △ Critical dimension: ∇

HM XX 50 X 0 XXXX G

No. OF POLES ———→ △ RoHS compliant (lead<4%) In copper Alloy

01: 1 POLES
02: 2 POLES
△ COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL 7004/P)
9 White(RAL1102)
C Multiple colors

24: 24 POLES
0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE				HM 5.08mm Series Dip solder			
PART NO.	HMxx50x0xxxxG			DWG NO.	8HM0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Da cheng 2013.05.28	Da cheng 2013.05.28				

Tolerance			
X.	±0.50		
X.X	±0.30		
X.XX	±0.10		
X°	±1°		