

| SIGN                                           | DATE | DESCRIPTION | APPROVER |
|------------------------------------------------|------|-------------|----------|
| △                                              |      |             |          |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |      |             |          |

Material:


- Item 1 Terminal (housing) : Thermoplastic (UL 94V-0)
- Item 2 Terminal (lever) : Thermoplastic (UL 94V-0)
- Item 3 Condom: Brass ,Ni plated
- Item 4 Wire guard : Brass ,Ni plated
- Item 5 Clamp : Brass ,Ni plated
- Item 6 Wire guard solder pin : Brass ,Tin plated
- Item 7 Terminal screw : Steel Zinc plating"-slot type

Electrical:

- Voltage rating : 300V
- Current rating : 15A
- Wire range :
- Solid wire (AWG) : 12-28
- Stranded wire(AWG) :12-28
- Torque(Lb-In) : 3.5
- Screw : M3
- Wire strip length :8~9mm
- Withstanding Voltage : 1.6KV
- Operating temperature : -40°C+115°C
- Soldering temperature : 250°C+10°C/5 Sec

VT xx 21 x 0 xxxx G

|                |                     |                                       |                       |
|----------------|---------------------|---------------------------------------|-----------------------|
| 01 1 CONTACTS  | 0 Black             | 0000:"@Logo (Standard)                | Pb < 40,000ppm (RoHS) |
| 02 2 CONTACTS  | 5 Green (RAL6018/T) | 000A:"ANYTEK"Logo                     |                       |
| ... ..         | 6 Blue (RAL7035/D)  | Any special item by customer request, |                       |
| 12 12 CONTACTS | 8 Grey              | please contact sales department.      |                       |




SECTION A--A

Dimension


|       |            |
|-------|------------|
| DIM A | N×5.08     |
| DIM B | (N-1)×5.08 |

N=Number of poles

| POLES  | TOL   |
|--------|-------|
| 1p-6p  | ±0.40 |
| 7p-12p | ±0.60 |



P.C.B LAYOUT



|          |                       |                     |                     |                                                                                                                                                                                           |             |            |           |
|----------|-----------------------|---------------------|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|------------|-----------|
| ANYTEK   |                       |                     |                     | CUSTOMER COPY                                                                                                                                                                             |             |            |           |
|          |                       |                     |                     | ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD |             |            |           |
| TITLE    | VT 5.08 Series 1P-12P |                     |                     |                                                                                                                                                                                           |             |            |           |
| PART NO. | VTxx21x0xxxxG         |                     |                     | DWG NO.                                                                                                                                                                                   | 8VT0001     |            |           |
| APPROVED | CHECKED               | DESIGNED            | DRAWN               | CUST NO.                                                                                                                                                                                  |             |            | Tolerance |
|          |                       | Aaron<br>2009.11.04 | Aaron<br>2009.11.04 |                                                                                                      | UNIT: mm    | X. ±0.50   |           |
|          |                       |                     |                     |                                                                                                                                                                                           | SCALE: NONE | X.X ±0.30  |           |
|          |                       |                     |                     | SHEET: 01/01                                                                                                                                                                              | REV: B      | X.XX ±0.10 |           |
|          |                       |                     |                     |                                                                                                                                                                                           |             | X* ±1"     |           |