



SCALANCE XF204, flat, Managed IE switch, 4x 10/100 Mbit/s RJ45 ports, Error signaling contact with set pushbutton, Redundant power supply, PROFINET IO device network management, Redundancy Manager integrated, incl. electron. manual on CD-ROM, C-plug optional.

product type designation	
product brand name	SCALANCE
product type designation	XF204
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	4
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	2.64 W
• supply voltage / 1 / rated value	18 ... 32 V
• consumed current / 1 / maximum	0.11 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	1.1 A / 33 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
• note	If the IE-Switch XF-200 is installed horizontally, a maximum ambient temperature of +40 °C is permitted
relative humidity	
• at 25 °C / without condensation / during operation /	95 %

maximum	
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	flat
width	75 mm
height	125 mm
depth	73 mm
net weight	0.25 kg
fastening method	
• 35 mm DIN-rail mounting	Yes
• wall mounting	No
• S7-300 rail mounting	No
• S7-1500 rail mounting	No
<b>product features, product functions, product components / general</b>	
cascading in the case of a redundant ring / at reconfiguration time of $<1\sim0.3\sim s$	50
cascading in cases of star topology	any (depending only on signal propagation time)
<b>product functions / management, configuration, engineering</b>	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• port mirroring	Yes
• multiport mirroring	No
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
<b>product functions / diagnostics</b>	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
<b>product functions / DHCP</b>	
product function	
• DHCP client	Yes
<b>product functions / redundancy</b>	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• ring redundancy	Yes
• high speed redundancy protocol (HRP) with redundancy	Yes

manager	
• high speed redundancy protocol (HRP) with standby redundancy	No
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
<b>product functions / security</b>	
protocol / is supported	
• SSH	Yes
<b>product functions / time</b>	
product function	
• SICLOCK support	Yes
protocol / is supported	
• NTP	No
• SNTP	Yes
<b>standards, specifications, approvals</b>	
certificate of suitability	
• CE marking	Yes
• KC approval	Yes
• Regulatory Compliance Mark (RCM)	Yes
standard	
• for EMC interference emission	EN 61000-6-4:2001 (Class A)
• for immunity to EMC	EN 61000-6-4:2001
• for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
<b>standards, specifications, approvals / hazardous environments</b>	
certificate of suitability	
• ATEX	Yes
• UKEX	Yes
• IECEx	Yes
• ULhazloc approval	Yes
• CCC / for hazardous zone according to GB standard	Yes
• FM registration	Yes
<b>standards, specifications, approvals / other</b>	
certificate of suitability	
• railway application in accordance with EN 50155	No
• railway application in accordance with EN 50124-1	No
• RoHS conformity	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	Yes
• French marine classification society (BV)	Yes
• DNV GL	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (NK)	Yes
• Polski Rejestr Statkow (PRS)	No
• Royal Institution of Naval Architects (RINA)	Yes
<b>standards, specifications, approvals / Environmental Product Declaration</b>	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total	100.09 kg
• during manufacturing	16.65 kg
• during operation	82.99 kg
• after end of life	0.45 kg
<b>product functions / general</b>	
MTBF	48.03 a
reference code	
• according to IEC 81346-2	KF
• according to IEC 81346-2:2019	KFE
Warranty period	5 a

product function / is supported / identification link		Yes; acc. to IEC 61406-1:2022			
further information / internet links					
internet link					
<ul style="list-style-type: none"><li>to website: Selection guide for cables and connectors</li><li>to web page: selection aid TIA Selection Tool</li><li>to website: Industrial communication</li><li>to web page: SiePortal</li><li>to website: Image database</li><li>to website: CAX-Download-Manager</li><li>to website: Industry Online Support</li></ul>		<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a> <a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a> <a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a> <a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a> <a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a> <a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>			
security information					
security information		Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit <a href="http://www.siemens.com/cybersecurity-industry">www.siemens.com/cybersecurity-industry</a> . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <a href="https://www.siemens.com/cert">https://www.siemens.com/cert</a> . (V4.7)			
Approvals / Certificates					
General Product Approval					
 EG-Konf.	<a href="#">Declaration of Conformity</a>	 CCC	 EAC	 UL	<a href="#">Miscellaneous</a>
General Product Approval		EMV		For use in hazardous locations	
 RCM	<a href="#">KC</a>	 IECEx	 ATEX	<a href="#">FM</a>	<a href="#">CCC-Ex</a>
Maritime application					
 ABS	 BUREAU VERITAS	 DNV	 LRS	<a href="#">NK / Nippon Kaiji Kyokai</a>	 PRS
Maritime application		Environment		Industrial Communication	
 RINA	<a href="#">Confirmation</a>	 EPD	<a href="#">PROFINET</a>		

last modified:

4/2/2025 