



SCALANCE XB205-3LD managed layer 2 IE switch 5x 10/100 Mbit/s RJ45 ports 3x SM FO SC-port 1x console port, diagnostics LED redundant power supply; IEC 62443-4-2 certified; temperature range 0 °C to +60 °C; DIN-rail mounting; default EtherNet/IP.

product type designation	
product brand name	SCALANCE
product type designation	XB205-3LD
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	5; RJ45
number of 100 Mbit/s SC ports	
• for single mode (LD)	3
transmission method / of the optical interface	100BaseLX LD
interfaces / other	
number of electrical connections	
• for operator console	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for management purposes	RJ45
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	7 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	0.29 A
• type of electrical connection / 1 / for power supply	6-pole terminal block
• product component / 1 / fusing at power supply input	Yes
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	80 mm
height	117 mm

depth	109 mm
net weight	0.35 kg
material / of the enclosure	Polycarbonate (PC-GF10)
fastening method	
• 35 mm DIN-rail mounting	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• configuration with STEP 7	Yes
• RMON	Yes
• port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
PROFINET conformity class	B
network load class / according to PROFINET	3
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• SFTP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
product functions / DHCP	
product function	
• DHCP client	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	

media redundancy protocol (MRP) with redundancy manager	Yes
Media Redundancy Protocol Interconnection (MRP-I)	Yes
of the PROFINET IO device / is supported / PROFINET system redundancy	No
ring redundancy	Yes
high speed redundancy protocol (HRP) with redundancy manager	Yes
high speed redundancy protocol (HRP) with standby redundancy	Yes
redundancy procedure STP	Yes
redundancy procedure RSTP	Yes
redundancy procedure RSTP+	Yes
Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
passive listening	Yes
product functions / security	
product function	
IEEE 802.1x (radius)	Yes
RADIUS client	Yes
broadcast/multicast/unicast limiter	Yes
broadcast blocking	Yes
protocol / is supported	
SSH	Yes
SSL	Yes
product functions / time	
product function	
SICLOCK support	Yes
NTP-client	Yes
SNTP client	Yes
protocol / is supported	
SNTP	Yes
standards, specifications, approvals	
certificate of suitability	
CE marking	Yes
KC approval	Yes
Regulatory Compliance Mark (RCM)	Yes
standard	
for EMC interference emission	EN 61000-6-4 (Class A)
for immunity to EMC	EN 61000-6-2
for safety / from CSA and UL	UL 60950-1 E115352, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
ATEX	Yes
UKEX	Yes
IECEX	Yes
ULhazloc approval	Yes
CCC / for hazardous zone according to GB standard	Yes
FM registration	Yes
standards, specifications, approvals / other	
certificate of suitability	
RoHS conformity	Yes
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
total	260.76 kg
during manufacturing	40.94 kg
during operation	219.31 kg
after end of life	0.51 kg
product functions / general	

MTBF	50 a
reference code	
• according to IEC 81346-2 • according to IEC 81346-2:2019	KF KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022

further information / internet links

internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com

security information

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
----------------------	---

Approvals / Certificates

General Product Approval



[Declaration of Con-
formity](#)



[Miscellaneous](#)

General Product Approval

EMV

For use in hazardous locations

[Declaration of Con-
formity](#)



[KC](#)



For use in hazardous locations

Environment

Industrial Communication

[FM](#)

[CCC-Ex](#)

[Confirmation](#)

[PROFINET](#)

last modified:

4/2/2025