

product type designation

product description

Foundation Fieldbus Cable

Bus cable (2-core), sold by the meter, unassembled

Foundation Fieldbus Cable; bus cable for IEC 61158-2; sheath color blue for Ex applications; 2-core shielded; stranded drain wire; Sold by the meter delivery unit max. 1000 m minimum order quantity 20 m.



suitability for use

For use in fieldbus systems according to IEC 61158-2 (e.g. Foundation Fieldbus), suitable for Ex applications

cable designation

2X(ST)CY 1X2X1.1/2.85-100 LI BL FR OE

wire length

sold by the meter

electrical data

attenuation factor per length

- at 38.4 kHz / maximum

0.003 dB/m

impedance

- rated value
- at 31.25 kHz
- at 38.4 kHz

100 Ω
100 Ω
100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 31.25 kHz
- of the characteristic impedance at 38.4 kHz

20 %
20 %

loop resistance per length / maximum

46 mΩ/m

shield resistance per length / maximum

10 Ω/km

capacity per length / at 1 kHz

65 pF/m

inductance per length

0.75 μH/m

operating voltage

- RMS value

300 V

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided shield of tin-plated copper wires with shield wire

type of electrical connection / FastConnect

No

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

1.17 mm
2.85 mm
6.4 mm
8.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

- of the wire insulation
- of cable sheath

polyethylene (PE)
PVC

color

- of the insulation of data wires
- of cable sheath

blue/brown
blue

bending radius

- with single bend / minimum permissible

34 mm

• with multiple bends / minimum permissible	68 mm
tensile load / maximum	100 N
weight per length	98 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +105 °C
• during storage	-40 ... +105 °C
• during transport	-40 ... +105 °C
• during installation	-40 ... +105 °C
• note	Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
ambient condition / for operation	Transfer rate of cable: 31.25 Kbit/s
fire behavior	flame resistant according to IEC 60332-1-2
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil	conditional resistance
• to grease	Conditional resistance
• to water	conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(UL)us, CMG / PLTC / Sun Res
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval	Yes
• RoHS conformity	Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase

customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert.> (V4.7)

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)

[Declaration of Conformity](#)



Test Certificates	Environment
-------------------	-------------

[Special Test Certificate](#)

[Confirmation](#)

[Environmental Confirmations](#)

last modified: 8/8/2024 