







P.C.B. LAYOUT
Bottom view



Dimension

DIM A	$N \times 5.08 \pm 0.9$
DIM B	$(N-1) \times 5.08$

N=Number of poles

POLES	DIM B	DIM A
1P		± 0.10
2p-6p	± 0.15	± 0.20
7p-12p	± 0.20	± 0.25
13p-18p	± 0.25	± 0.30
19p-24p	± 0.35	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/27'07	The Soldering temperature from 245° to 250°	Aaron
△	10/09'12	Update the drawing	Da cheng
△	04/18'13	Update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Terminal body (Contact pin): Brass, Tin plated
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Cover: Thermoplastic (UL94V-0)
- Item ④ Terminal Body: Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
 - Solid wire(AWG): 12-28
 - Stranded wire(AWG): 12-28
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

HG xx 30 x 0 xxxx G			RoHS compliant (lead<4%) In copper Alloy
Poles	Color		
01 1Contacts	0 Black (RAL9005)		0000 Standard @ Logo
02 2Contacts	2 Red (RAL3001/D)		000A Standard ANY Logo
	3 Orange(RAL2011/P)		Any special item by
	4 Yellow(RAL1018/A)		customer request,
	5 Green(RAL6018/T)		please contact sales
	6 Blue (RAL5015/A)		department.
	8 Grey(RAL7004/P)		
	9 White(RAL1102)		
24 24Contacts	C Multiple colors		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HG 5.08mm Series							
PART NO.	HGxx30x0xxxxG			DWG NO.	8HG0101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Da cheng 2013.04.18	Da cheng 2013.04.18		UNIT: mm		X. ±0.50	
					SCALE: NONE		X.X ±0.30	
					REV.: F		X.XX ±0.10	
				SHEET: 01/01	X° ±1°			