



Figure similar

Integrated signal lamp, single flash light, w. built-in electronic flash, yellow, 230 V AC, Diameter 70 mm

General technical data			
product designation		Flashlight element	
consumed current maximum		35 mA	
type of voltage of the operating voltage		AC	
operating voltage			
• 1 at AC at 50 Hz rated value		230 V	
• 1 at AC at 60 Hz rated value		230 V	
relative positive tolerance of the operating voltage		10 %	
relative negative tolerance of the operating voltage		-10 %	
reference code according to IEC 81346-2		P	
fastening method		Bayonet / flush mounting	
material		PC; PC/ABS; PA	
color		yellow	
Mechanical data			
product component light source		Yes	
type of electrical connection		screw terminal	
outer diameter of the signal column element		75 mm	
Lamp			
design of the optical signal		flash light	
type of light source		Xenon gas discharge lamp	
light intensity		21 870 cd	
flash frequency		1 Hz	
number of flashes of light element		4 000 000	
Ambient conditions			
ambient temperature during operation		-20 ... +50 °C	
protection class IP		IP65	
depth		31 mm	
height		66 mm	
width		75 mm	
Certificates/ approvals			
General Product Approval		other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5350-0CD>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5350-0CD>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5350-0CD>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5350-0CD&lang=en





last modified:

4/1/2025 