







PCB Layout

N = Number of poles.

$$\Delta \text{Dim.A} = N \times 7.5 - 1.5$$

$$\text{Dim.B} = (N - 1) \times 7.5$$

POLE	4x2 ~ 4x4	4x5 ~ 4x8	4x9 ~ 4x12	4x12 ~ 4x16
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	2014.09.10	Upgrade the picture	Airy min

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Insulator(Cover): Thermoplastic (UL94V-0)
- Item 2 Insulator(housing): Thermoplastic (UL94V-0)
- Item 3 Spring clamp: Stainless steel
- Item 4 Solder Pin (The fourth layer): Brass, Tin plated
- Item 5 Solder Pin (The third layer): Brass, Tin plated
- Item 6 Solder Pin (The second layer): Brass, Tin plated
- Item 7 Solder Pin (The first layer): Brass, Tin plated
- Item 8 Insulator(pad board): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus
- Critical dimension: △

HS xx 10 x 0 xxxx G

No. OF POLES

G: Pb<4000ppm

08: 4x2 POLES

60: 4x15 POLES

64: 4x16 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

8: GREY (RAL 7004/P)

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HS 7.5mm Series (Solder pins in line)						
PART NO.		HSxx10x0xxxxG			DWG NO.	8HS0201		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Airy min 2014.09.10	Airy min 2014.09.10			UNIT: mm	X.	±0.50
						SCALE: NONE	X.X	±0.30
						REV.: C	X.XX	±0.10
SHEET: 01/01								