



P.C.B. LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard :stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

Electrical UL / CSA

- Voltage rating: 125V/125V
- Current rating: 10A/10A
- Wire range:
- Solid wire(AWG): 16-26 / 16-26
- Stranded wire(AWG): 16-26 / 16-26
- Torque: 1.7Lb-In/4kgf.cm
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.25KV/1.25KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

TF xx 0 1 x x xxxx G

POLES
02 02 POLES
03 03 POLES
...
24 24 POLES

COLOR
0 BLACK
5 GREEN(RAL6018/T)
6 BLUE
8 Grey(RAL7035/D)
C GREEN(RAL6018/U)

DIM A Length
0 4.4mm
1 3.8mm
2 3.5mm

G RoHS compliant
(Lead <4%)
In copper Alloy
000 0 @ logo
000 A ANY logo
Any special item by
customer request,
please contact sales
department.

Poles Dim	02	03	04	05	06	07	08	09	10	11	12	13
Dim L	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00	45.50
Dim B	3.50	7.00	10.50	14.00	17.50	21.00	24.50	28.00	31.50	35.00	38.50	42.00
TOL	±0.15				±0.20				±0.25			
Poles Dim	14	15	16	17	18	19	20	21	22	23	24	
Dim L	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	84.00	
Dim B	45.50	49.00	52.50	56.00	59.50	63.00	66.50	70.00	73.50	77.00	80.50	
TOL	±0.25		±0.35				±0.40					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		TF 3.5 series “-”				DWG NO.		8TF0101	
PART NO.		TFxx01xxxxxxG				DWG NO.		8TF0101	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance
			Guoxue 2012.11.09	Guoxue 2012.11.09			UNIT: mm	X.X	±0.50
					SHEET: 01/01		SCALE: NONE	X.XX	±0.30
							REV.: B	X°	±0.10
									±1°