



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switch. 3-Pole 3-Wire Fused in a type 4/4X 304 grade Stainless Steel enclosure. Rated 240VAC (100A). Special features: Crouse-Hinds interlocked receptacle.

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	3
suitability for operation	PROTECTION OF HEAVY DUTY PORTABLE EQUIPMENT
Electricity	
ampacity	100 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
special product feature	ACCEPTS CROUSE-HINDS Arktite PLUGS
type of electrical connection	INTERLOCKED PLUG
Mechanical Design	
design of the housing	TYPE 4X
design of the actuating element	SINGLE THROW
material	304 STAINLESS STEEL
General product approval	
certificate of suitability	UL98

last modified: 9/15/2021 

