


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	NEW RELEASE		3/DEC/2013	
A1	Added ACD PIN to the table.		24/Oct/2019	




Reverse Polarity TNC Male

Type N Male

LENGTH & P/N Table

LENGTH	CUSTOMER P/N
3FT(914±30mm)	CO-058TNCRPTN-003
6FT(1829±40mm)	CO-058TNCRPTN-006
10FT(3048±40mm)	CO-058TNCRPTN-010
15FT(4572±50mm)	CO-058TNCRPTN-015
25FT(7620±100mm)	CO-058TNCRPTN-025



SECTION A-A

- NOTES:
- 1.CABLE:[20AWG(19/0.18±0.008mm)*1C+AL/MYLAR +BRAID(16*8/0.12±0.008mm)]TINNED COPPER INSULATION:PE OD= 2.95±0.10mm COLOR:TRANSPARENT JACKET:HALF MATTE PVC LOW TOXIC; OD=Ø5.0±0.15mm COLOR:UL813 BLACK
 - 2.CONNECTOR:Reverse Polarity TNC Male N PLUG CRIMP FOR RG58U
 - 3.OPEN/SHORT MISS WIRE TEST 100%
 - 4.CONDUCTOR RESISTANCE ≤ 36.7Ω/km
 - 5.INSULATION RESISTANCE ≥ 2MΩ DC300V 0.01Sec
- ALL MATERIALS SHALL ACCORD WITH RoHS STANDARD.

PIN OUT:

CENTER	CENTER
SHELL	SHELL



NOTES: UNLESS OTHERWISE SPECIFIED

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:		E&R NO.		Amphenol Cables on Demand 20 VALLEY ST. ENDICOTT, NY 13760	
DETAILED		APPROVALS		DATE	
X ±X		LF		3/DEC/2013	
XX ±XX		CHECKED BA		3/DEC/2013	
XXX ±XXX		RESP ENG			
THIRD ANGLE PROJECTION		DRAWING		SIZE DWG. NO.	
		A		CO-058TNCRPTN-XXX	
		SCALE		SHEET OF	
				REV. A1	