



Control Power Transformer, 100va, PRI 115x230v, SEC 24v, Domestic,

product brand name	Control Power Transformer
design of the product	Control power voltage
special product feature	Robust design
General technical data	
weight [lb]	3.5 lb(av)
Height x Width x Depth [in]	3.46 × 3.31 × 4.11 in
ambient temperature [°F] during operation	-4 ... +104 °F
ambient temperature during operation	-20 ... +40 °C
country of origin	Mexico
operating apparent power rated value	100 VA
Enclosure	
design of the housing	Open
Mounting/wiring	
mounting position	Any
fastening method	Surface mounting
type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)
type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
Inputs/ Outputs	
input variables of primary voltage	115x230vac
output dimensions of secondary voltage	24vac
phase number of the inputs	1
electrical input frequency	50 ... 60 Hz
input voltage _1	115 V
input voltage _2	230 V
phase number of the outputs	1
electrical output frequency	60 ... 50 Hz
output voltage _1 rated value	24 V
certificate of suitability	UL / CSA
Approvals Certificates	
Test Certificates	



Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MT0100D>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0100D>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:MT0100D&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT0100D/certificate>

last modified:

5/31/2021 