




RoHS Compliant

The color of lever is consistent with body's



N=NUMBER OF POLES

DIM		TOL			
		2P--6P	7P--12P	13P--18P	19P--24P
Dim L	N×3.5+0.70	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×3.5	±0.15	±0.20	±0.30	±0.40

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	10/28'19	The first release	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item (a) Lever: High temp. polyamide (UL94V-0)
- Item (b) Terminal housing: High temp. polyamide (UL94V-0)
- Item (c) Wire guard: Stainless steel
- Item (d) Solder Pin: Brass.Tin plated

Electrical: cULus

- Voltage rating: 300 V
- Current rating(SOL): 7 A
- Current rating(STR): 10 A
- Wire range:
- Solid wire(AWG): 18-24
- Stranded wire(AWG): 16-22
- Wire strip length: 12-13 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +110°C
- Reflow Soldering temperature: 260°C/10 Sec Max.
- Safety Approval:
- Critical dimension:

NM xx 1 0 x A xxxx G

No. OF POLES

02 2 Poles

03 3 Poles

... ..

24 24 Poles

Color

0 Black (RAL9005)

RoHS compliant
(lead<4%)

In copper Alloy

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NM 3.5 Series Vertical 90° wire inlet THT			
PART NO.	NMxx10xAxxxxG			DWG NO.	8NM0007
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Guoxue 2019.10.28	Guoxue 2019.10.28		Tolerance
				UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				SHEET: 01/01	X.XX ±0.10
				REV.: B	X° ±1°