






RoHS Compliant

The color of lever is consistent with body's



Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	7/28'25		Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item (A) Lever: High temp. polyamide (UL94V-0)
- Item (B) Terminal housing: High temp. polyamide (UL94V-0)
- Item (C) Wire guard: Stainless steel
- Item (D) Solder Pin: Brass.Tin plated

Electrical:

cULus

- Voltage rating: 300 V
- Current rating(SOL): 7 A
- Current rating(STR): 10 A
- Wire range:
- Solid wire(AWG): 18-24
- Stranded wire(AWG): 16-22
- Wire strip length: 12-13 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -45°C to +130°C
- Reflow Soldering temperature: 260°C/10 Sec Max.
- Safety Approval: cULus
- Critical dimension: 15.1 REF

NM xx 1 0 x B xxx G

No. OF POLES
02 2 Poles
03 3 Poles
...
24 24 Poles

Color
0 Black (RAL9005)

RoHS compliant
(lead<4%)
In copper Alloy
0000: "A" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

N=NUMBER OF POLES

DIM.		TOL.			
		2P--6P	7P--12P	13P--18P	19P--24P
Dim L	N×3.5+0.70	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×3.5	±0.15	±0.20	±0.30	±0.40

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NM 3.5 Series Horizontal 180° wire inlet THT			
PART NO.	NMxx10xBxxxxG			DWG NO.	8NM0204
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
			Guoxue 2025.07.28		
				SHEET: 01/01	Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°