




SETRON, Switch disconnecter 3LD, emergency switching-off switch, 6- pole, $I_n=250$ A, operating power / at AC-23 A 400 V: 132 kW, floor mounting with door coupling, knob-operated mechanism, red/yellow, 4-hole mounting of the handle

Model	
product brand name	SETRON
product designation	Switch disconnecter
design of the product	EMERGENCY-STOP switch
display version for switch position indicator manual operation	1 ON - 0 OFF
type of switch	Floor mounting with door coupling
design of the actuating element	selector switch
color of the actuating element	red
design of handle	knob-operated mechanism, red/yellow
type of the driving mechanism motor drive	No
General technical data	
number of poles	6
size of switch disconnecter	5
mechanical service life (operating cycles) typical	100 000
electrical endurance (operating cycles)	
• at AC-23 A at 690 V	6 000
operating frequency maximum	50 1/h
degree of pollution	3
Voltage	
insulation voltage rated value	690 V
surge voltage resistance rated value	8 kV
operating voltage	
• at AC rated value	690 V
operating frequency rated value	
• minimum	50 Hz
• maximum	60 Hz
Protection class	
protection class IP	IP65
degree of protection NEMA rating	1, 3R, 4X, 12
protection class IP on the front	IP65
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	36 W
Main circuit	
operational current	
• at AC-21 at 690 V rated value	250 A
• at AC-21 A at 240 V rated value	250 A
• at AC-21 A at 400 V rated value	250 A
• at AC-21 A at 440 V rated value	250 A

• at AC-23 A at 400 V rated value	224 A
operating power	
• at AC-23 A at 240 V rated value	75 kW
• at AC-23 A at 400 V rated value	132 kW
• at AC-23 A at 440 V rated value	132 kW
• at AC-23 A at 690 V rated value	55 kW
• at AC-3 at 240 V rated value	55 kW
• at AC-3 at 400 V rated value	110 kW
• at AC-3 at 690 V rated value	45 kW
Auxiliary circuit	
number of CO contacts for auxiliary contacts	0
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
operating voltage of auxiliary contacts at AC maximum	500 V
continuous current of the auxiliary contact rated value	10 A
insulation voltage of the auxiliary switch rated value	500 V
Suitability	
suitability for use main switch	Yes
suitability for use switch disconnecter	Yes
suitability for use EMERGENCY OFF switch	Yes
suitability for use safety switch	Yes
suitability for use maintenance/repair switch	Yes
Product details	
product feature can be locked into OFF position	Yes
Accessories	
product extension optional	
• motor drive	No
• voltage trigger	No
number of connectable NC contacts for auxiliary contacts attachable maximum	3
number of connectable NO contacts for auxiliary contacts attachable maximum	5
number of connectable CO contacts for auxiliary contacts attachable maximum	0
number of bracket locks maximum	3
hasp thickness of the bracket locks	4 ... 6 mm
Short circuit	
conditional short-circuit current with line-side fuse protection	
• at 690 V by gG fuse rated value	50 kA
let-through current with closed switch	
• at 240 V for combination switch + gG fuse maximum	15 kA
• at 440 V for combination switch + gG fuse maximum	15 kA
• at 690 V for combination switch + gG fuse maximum permissible	15 kA
I²t value with closed switch	
• at 240 V for combination switch + gG fuse maximum	557 kA ² .s
• at 440 V for combination switch + gG fuse maximum	557 kA ² .s
• at 690 V for combination switch + gG fuse maximum	557 kA ² .s
design of the fuse link	
• for short-circuit protection of the main circuit required	fuse gL/gG: 250 A
• for short-circuit protection of the auxiliary switch required	fuse gL/gG: 10 A
operational current of upstream fuse rated value	250 A
according UL	
operational current at AC according to UL 508/UL 60947-4-1 rated value	250 A
operating voltage at AC at 50/60 Hz according to UL 508/UL 60947-4-1 rated value	600 V
active power [hp] at AC at 480 V according to UL 508/UL 60947-4-1 rated value	100
active power [hp] at AC at 600 V according to UL 508/UL 60947-4-1 rated value	75
short-time withstand current (SCCR) at 600 V according to	10 kA

UL 508/UL 60947-4-1		
continuous current of upstream fuse according to UL rated value		200 A
type of fuse according to UL		RK5
Connections		
AWG number as coded connectable conductor cross section solid maximum		
•		1
•		4/0
type of connectable conductor cross-sections for copper conductor		
• solid		1x (16 ...185mm²)
• finely stranded with core end processing		1x (16...150mm²)
• stranded		1x (16...185mm²)
type of connectable conductor cross-sections for auxiliary contacts		
• solid		lateral auxiliary switch 2x (0,75 ... 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 ... 2,5mm²)
• finely stranded with core end processing		lateral auxiliary switch 2x (0,75 ... 1,5mm²), 1x 2,5mm²; front auxiliary switch 1x 2,5mm²
• stranded		lateral auxiliary switch 2x (0,75 ... 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 ... 2,5mm²)
type of electrical connection		
• for main current circuit		box terminal
• for auxiliary contacts		connection terminals
Mechanical Design		
height		169 mm
width		112 mm
depth		94 mm
type of device		fixed mounting
fastening method		Built-in unit fixed-mounted version
fastening method		
• 4-hole front mounting		Yes
• front mounting with central attachment		No
• rail mounting		No
Net Weight		4.557 kg
Environmental conditions		
ambient temperature during operation		
• minimum		-25 °C
• maximum		55 °C
ambient temperature during storage		
• minimum		-25 °C
• maximum		55 °C
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Environmental Confirmations](#)

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

<http://www.siemens.com/lowvoltage/catalogs>

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2418-3VK13>

<https://support.industry.siemens.com/cs/ww/en/ps/3LD2418-3VK13>

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2418-3VK13

<http://www.siemens.com/cax>

<http://www.siemens.com/specifications>

