





ROHS Compliant



"a" LOGO



SECTION A-A

DIM (n=Number of poles)		TOL		
		2P-3P	4P-6P	7P-12P
Dim N	n*5.0	±0.15	±0.20	±0.25
Dim M	(n-1)*5.0	±0.15	±0.20	±0.25

XD xx 7 0 x 0 xxxxx G

02 2poles
03 3poles
...
12 12poles

Body color
0 Black
2 Red
3 Orange
4 Yellow
5 Green
6 Blue
8 Grey
9 White

0000 standard @ logo
Any special item by customer request, please contact sales department

G ROHS compliant (lead<4% in copper alloy)

PRELIMINARY

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
A1	-	2024.11.27	The first release	Jesse
THIS IS CREO DRAWING, DO NOT REVISE MANUALLY!!!				

Notes:

	UL1059 Group B	Group D	/ TUV
● Rated Voltage:	300V	300V	320V
● Rated Current:	8A	8A	10A
● Wire range :	AWG 26-14		0.2-2.5mm ²
● Rated impulse voltage :			4kV
● Withstanding Voltage :	1.6kV 1min		
● Wire strip length :	8-9mm		
● Operating temperature :	-40 °C to +100 °C		
● Safety approval:	cULus		

5	Spring clamp	Stainless steel	n
4	Terminal	C7025,Sn(4-8μm) Ni(0.75μm Min) plated,	n
3	Cover	PA66(UL 94 V-0)	1
2	Lever	PA66(UL 94 V-0),Orange (RAL2011/P)	n
1	Body	PA66(UL 94 V-0)	1
ITEM	PART NAME	DESCRIPTION	Q'TY

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE:	XD 5.0 Series						
PART NO.	XDxx70x0xxxxG			DWG NO.	8XD0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Jesse	Petter				
		20241127	2023.10.16				
				SHEET: 1 / 1			
					UNIT: mm	Tolerance	
					SCALE: 1.5:1	X. ±0.5	
					REV.: A1	X.X ±0.3	
						X.XX ±0.1	
						X° ±0.1°	