

STARTER, 3RE41235CA354WB0, WITH MODS



|                                                                          |                               |
|--------------------------------------------------------------------------|-------------------------------|
| product brand name                                                       | Siemens                       |
| product designation                                                      | Non-reversing motor starter   |
| special product feature                                                  | Start-Stop Push Buttons       |
| <b>General technical data</b>                                            |                               |
| weight [lb]                                                              | 21 lb(av)                     |
| Height x Width x Depth [in]                                              | 14 × 12 × 8 in                |
| touch protection against electrical shock                                | NA for enclosed products      |
| installation altitude [ft] at height above sea level maximum             | 6 560 ft                      |
| country of origin                                                        | Germany                       |
| <b>Power and control electronics</b>                                     |                               |
| number of poles for main current circuit                                 | 3                             |
| type of voltage of the control supply voltage                            | AC                            |
| control supply voltage                                                   |                               |
| • at AC at 50 Hz rated value                                             | 110 V                         |
| • at AC at 60 Hz rated value                                             | 120 V                         |
| disconnecter functionality                                               | No                            |
| yielded mechanical performance [hp] for 3-phase AC motor                 |                               |
| • at 200/208 V rated value                                               | 10 hp                         |
| • at 220/230 V rated value                                               | 15 hp                         |
| • at 460/480 V rated value                                               | 30 hp                         |
| • at 575/600 V rated value                                               | 40 hp                         |
| <b>Contactors</b>                                                        |                               |
| number of NO contacts for main contacts                                  | 3                             |
| operating voltage at AC-3 rated value maximum                            | 600 V                         |
| mechanical service life (operating cycles) of the main contacts typical  | 10 000 000                    |
| <b>Auxiliary contact</b>                                                 |                               |
| number of NC contacts for auxiliary contacts                             | 1                             |
| number of NO contacts for auxiliary contacts                             | 1                             |
| number of total auxiliary contacts maximum                               | 8                             |
| contact rating of auxiliary contacts of contactor according to UL        | 10A@600V(A600), 5A@600V(P600) |
| <b>Coil</b>                                                              |                               |
| apparent pick-up power of magnet coil at AC                              | 188 VA                        |
| apparent holding power of magnet coil at AC                              | 16.5 VA                       |
| operating range factor control supply voltage rated value of magnet coil | 0.8 ... 1.1                   |
| ON-delay time                                                            | 10 ... 80 ms                  |
| OFF-delay time                                                           | 10 ... 18 ms                  |
| <b>Overload relay</b>                                                    |                               |
| product function                                                         |                               |

|                                                                                                                                                                                                                                |                                        |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|
| <ul style="list-style-type: none"> <li>• overload protection</li> <li>• phase failure detection</li> <li>• asymmetry detection</li> <li>• ground fault detection</li> <li>• test function</li> <li>• external reset</li> </ul> | Yes<br>Yes<br>Yes<br>Yes<br>Yes<br>Yes |
| reset function                                                                                                                                                                                                                 | Manual, automatic and remote           |
| trip class                                                                                                                                                                                                                     | CLASS 5 / 10 / 20 / 30                 |
| adjustment range of thermal overload trip unit                                                                                                                                                                                 | 20 ... 80                              |
| number of NC contacts of auxiliary contacts of overload relay                                                                                                                                                                  | 1                                      |
| number of NO contacts of auxiliary contacts of overload relay                                                                                                                                                                  | 1                                      |
| operational current of auxiliary contacts of overload relay <ul style="list-style-type: none"> <li>• at AC at 600 V</li> <li>• at DC at 250 V</li> </ul>                                                                       | 5 A<br>1 A                             |
| contact rating of auxiliary contacts of overload relay according to UL                                                                                                                                                         | 5A@600VAC (B600), 1A@250VDC (R300)     |
| insulation voltage (Ui) <ul style="list-style-type: none"> <li>• with single-phase operation at AC rated value</li> <li>• with multi-phase operation at AC rated value</li> </ul>                                              | 600 V<br>300 V                         |
| <b>Enclosure</b>                                                                                                                                                                                                               |                                        |
| degree of protection NEMA rating of the enclosure                                                                                                                                                                              | NEMA 3/3R/4/12 enclosure               |
| design of the housing                                                                                                                                                                                                          | Dust- & watertight for outdoor use     |
| <b>Mounting/wiring</b>                                                                                                                                                                                                         |                                        |
| mounting position                                                                                                                                                                                                              | Vertical                               |
| fastening method                                                                                                                                                                                                               | Surface mounting and installation      |
| type of electrical connection for supply voltage line-side                                                                                                                                                                     | Box lug                                |
| tightening torque [lbf-in] for supply                                                                                                                                                                                          | 26 ... 39 lbf-in                       |
| type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded                                                                                                                              | 2x (18 ... 2), 1x (18 ... 1)           |
| temperature of the conductor for supply maximum permissible                                                                                                                                                                    | 60 °C                                  |
| material of the conductor for supply                                                                                                                                                                                           | CU                                     |
| type of electrical connection for load-side outgoing feeder                                                                                                                                                                    | Box lug                                |
| tightening torque [lbf-in] for load-side outgoing feeder                                                                                                                                                                       | 26 ... 39 lbf-in                       |
| type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded                                                                                                             | 2x (18 ... 2), 1x (18 ... 1)           |
| temperature of the conductor for load-side outgoing feeder maximum permissible                                                                                                                                                 | 60 °C                                  |
| material of the conductor for load-side outgoing feeder                                                                                                                                                                        | CU                                     |
| type of electrical connection of magnet coil                                                                                                                                                                                   | Screw-type terminals                   |
| tightening torque [lbf-in] at magnet coil                                                                                                                                                                                      | 7 ... 10 lbf-in                        |
| type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded                                                                                                                            | 2x (20 ... 16), 2x (18 ... 14)         |
| temperature of the conductor at magnet coil maximum permissible                                                                                                                                                                | 75 °C                                  |
| material of the conductor at magnet coil                                                                                                                                                                                       | CU                                     |
| type of electrical connection for auxiliary contacts                                                                                                                                                                           | Screw-type terminals                   |
| tightening torque [lbf-in] at contactor for auxiliary contacts                                                                                                                                                                 | 7 ... 10 lbf-in                        |
| type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded                                                                                                       | 2x (20 ... 16), 2x (18 ... 14)         |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible                                                                                                                                           | 75 °C                                  |
| material of the conductor at contactor for auxiliary contacts                                                                                                                                                                  | CU                                     |
| tightening torque [lbf-in] at overload relay for auxiliary contacts                                                                                                                                                            | 7 ... 10 lbf-in                        |
| type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded                                                                                                  | 1x (20 ... 14), 2x (20 ... 14)         |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible                                                                                                                                      | 75 °C                                  |
| material of the conductor at overload relay for auxiliary contacts                                                                                                                                                             | CU                                     |
| <b>Short-circuit current rating</b>                                                                                                                                                                                            |                                        |
| design of the fuse link for short-circuit protection of the main circuit required                                                                                                                                              | Class J                                |
| design of the short-circuit trip                                                                                                                                                                                               | Thermal magnetic circuit breaker       |
| maximum short-circuit current breaking capacity (Icu) <ul style="list-style-type: none"> <li>• at 240 V</li> </ul>                                                                                                             | 5 kA                                   |

- at 480 V
- at 600 V

5 kA

5 kA

certificate of suitability

UL 60947-4-1

#### Approvals Certificates

| General Product Approval | Test Certificates | other | Dangerous goods | Environment |
|--------------------------|-------------------|-------|-----------------|-------------|
|--------------------------|-------------------|-------|-----------------|-------------|



[Confirmation](#)

[Transport Information](#)

[Environmental Confirmations](#)

#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4123-5CA35-4WB0>

Search Datasheet in Service&Support (Manuals)


<https://support.industry.siemens.com/cs/US/en/ps/3RE4123-5CA35-4WB0/man>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RE4123-5CA35-4WB0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4123-5CA35-4WB0&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/3RE4123-5CA35-4WB0/certificate>



last modified:

4/15/2021 