



ASIsafe SlimLine Compact module SC17.5F digital safety 2 F-DI/2 DQ, IP20 2 x input for mechanical sensors 2 x standard output 24 V DC Output supply can be switched spring-type terminals Width 17.5 mm

product designation	Slimline Compact I/O module for use in the control cabinet
design of the product	AS-i SC17.5F, 2F-DI/2DQ
product type designation	3RK1
design of the slave type	standard slave
AS-Interface slave profile	S-7.B.F
ID1 code	F; Factory setting, changeable
operating voltage according to AS-Interface specification	18 ... 31.6 V
product function suitable for AS-i Power24V	Yes
consumed current from profile conductors of the AS-Interface	
• at 30 V maximum	270 mA
• at 24 V with AS-i Power24V maximum	270 mA
type of address setting of AS-i slaves	via front addressing socket
Substance Prohibitance (Date)	05/01/2012
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol - 119-47-1
Weight	0.165 kg
reference code	
• according to EN 61346-2	K
• according to DIN 40719 extended according to IEC 204-2 according to IEC 750	A
shock resistance	15g / 11 ms (modules) or 10g / 11 ms (modules with device connector)
other information	An auxiliary external feed (AUX POWER) of between 20 and 30 V DC is necessary for supplying the output circuits. The auxiliary feed must comply with IEC 60990 (PELV), protection class III.
Digital Inputs	
number of digital inputs	0
number of digital inputs safety-related	2
type of input characteristic	mechanical contacts
Digital Outputs	
number of digital outputs	2
type of switching output	PNP transistor
product function for power supply reverse polarity protection	Yes
property of the output short-circuit proof	Yes
product function	Built-in induction protection
total current of digital outputs per module maximum	0.5 A
• note	0.2 A with supply via AS interface / 0.5 A with supply via Uaux
type of voltage supply at the outputs	AS interface / U_AUX switchable
ampacity of the semiconductor output at DC-13 at 24 V	0.5 A; 0.15 A with supply via AS interface / 0.5 A with supply via Uaux
Analog inputs	

number of analog inputs	0				
Analog outputs					
number of analog outputs	0				
ISO 13849					
performance level (PL) according to EN ISO 13849-1	PL e				
category according to EN ISO 13849-1	up to Category 4				
IEC 61508					
Safe failure fraction (SFF)	99 %				
Device connector					
ampacity of the interface to the device connector					
• for AS-Interface	2 A				
• for external auxiliary voltage	4 A				
Installation/ mounting/ dimensions					
fastening method	screw and snap-on mounting				
height	100 mm				
width	17.5 mm				
depth	120 mm				
Ambient conditions					
ambient temperature					
• during operation	-25 ... +70 °C				
• during storage	-40 ... +85 °C				
Connections/ Terminals					
type of electrical connection of the inputs and outputs	spring-loaded terminal (push-in)				
type of connectable conductor cross-sections					
• solid	1x (0.5 ... 1.5 mm²), 2x (0.5 ... 1.5 mm²)				
• finely stranded with core end processing	1x (0,25 ... 1,0 mm²), 2x (0,25 ... 1,0 mm²)				
• finely stranded without core end processing	1x (0.5 ... 1.5 mm²), 2x (0.5 ... 1.5 mm²)				
• for AWG cables solid	1x (20 ... 16), 2x (20 ... 16)				
• for AWG cables stranded	1x (20 ... 16), 2x (20 ... 16)				
Approvals Certificates					
General Product Approval	EMV	Test Certificates			
 EG-Konf.		 UL		 RCM	Type Test Certificates/Test Report
Marine / Shipping		other	Environment		
 ABS	 DNV	 LRS	 PRS	Confirmation	Environmental Confirmations
Industrial Communication					
 ASi					
Further information					
Siemens is working on the renewal of the current EAC certificates. Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus). Siemens has decided to exit the Russian market (see here). https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875 Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10 Industry Mall (Online ordering system)					

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1405-2BG00-2AA2>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1405-2BG00-2AA2>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1405-2BG00-2AA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1405-2BG00-2AA2&lang=en





last modified:

4/2/2025 