

Siemens  
EcoTech



Key-operated switch O.M.R, 22 mm, round, plastic, lock number 73037, red, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, Key removal O+I Z=50-unit packaging



|                                                    |                                    |
|----------------------------------------------------|------------------------------------|
| product brand name                                 | SIRIUS ACT                         |
| product designation                                | Key-operated switches              |
| design of the product                              | Actuating/signaling element        |
| product type designation                           | 3SU1                               |
| product line                                       | Plastic, black, 22 mm              |
| manufacturer's article number of included key      | <a href="#">3SU1950-0FK20-0AA0</a> |
| <b>Actuator</b>                                    |                                    |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)    |
| product extension optional light source            | No                                 |
| color                                              |                                    |
| • of the actuating element                         | red                                |
| material of the actuating element                  | metal                              |
| shape of the actuating element                     | Key                                |
| outer diameter of the actuating element            | 29.5 mm                            |
| number of switching positions                      | 2                                  |
| switch position for key distraction                | O+I                                |
| actuating angle                                    |                                    |
| • clockwise                                        | 90°                                |
| lock make                                          | O.M.R.                             |
| key number                                         | 73037                              |
| <b>Front ring</b>                                  |                                    |
| product component front ring                       | Yes                                |
| design of the front ring                           | Standard                           |
| material of the front ring                         | plastic                            |
| color of the front ring                            | black                              |
| <b>General technical data</b>                      |                                    |
| protection class IP                                | IP66, IP67, IP69(IP69K)            |
| protection class IP of the terminal                | IP20                               |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13         |
| shock resistance                                   |                                    |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms   |
| • for railway applications according to EN 61373   | Category 1, Class B                |
| vibration resistance                               |                                    |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                  |
| • for railway applications according to EN 61373   | Category 1, Class B                |
| operating frequency maximum                        | 1 800 1/h                          |
| mechanical service life (operating cycles) typical | 1 000 000                          |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| reference code according to IEC 81346-2                        | S                                                                  |
| Substance Prohibittance (Date)                                 | 10/01/2014                                                         |
| Weight                                                         | 90 g                                                               |
| <b>Ambient conditions</b>                                      |                                                                    |
| ambient temperature                                            |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| <b>Environmental footprint</b>                                 |                                                                    |
| Environmental Product Declaration (EPD)                        | Yes                                                                |
| global warming potential [CO2 eq] total                        | 0.787 kg                                                           |
| global warming potential [CO2 eq] during manufacturing         | 0.566 kg                                                           |
| global warming potential [CO2 eq] during operation             | 0.235 kg                                                           |
| global warming potential [CO2 eq] after end of life            | -0.015 kg                                                          |
| Siemens Eco Profile (SEP)                                      | Siemens EcoTech                                                    |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                    |
| height                                                         | 29.5 mm                                                            |
| width                                                          | 29.5 mm                                                            |
| shape of the installation opening                              | round                                                              |
| mounting diameter                                              | 22.3 mm                                                            |
| positive tolerance of installation diameter                    | 0.4 mm                                                             |
| mounting height                                                | 51.7 mm                                                            |
| installation width                                             | 29.5 mm                                                            |
| installation depth                                             | 25.4 mm                                                            |
| <b>Approvals Certificates</b>                                  |                                                                    |
| General Product Approval                                       | Test Certificates                                                  |



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other

Environment

[Confirmation](#)



Siemens  
EcoTech



[Environmental Confirmations](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1000-4FF11-0AA0-Z X90>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1000-4FF11-0AA0-Z X90>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1000-4FF11-0AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1000-4FF11-0AA0-Z X90&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1000-4FF11-0AA0-Z X90&lang=en)



---

last modified:

4/1/2025 