



Twin pushbutton, 22 mm, round, plastic with metal front ring, black, black, pushbuttons, flat, with laser labeling, upper case and lower case, always upper case at the beginning of the word

|                                                    |                                                                                               |
|----------------------------------------------------|-----------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                    |
| product designation                                | Twin pushbuttons                                                                              |
| design of the product                              | Actuating/signaling element                                                                   |
| product type designation                           | 3SU1                                                                                          |
| product line                                       | Plastic with metal front ring, matt, 22 mm                                                    |
| <b>Enclosure</b>                                   |                                                                                               |
| number of command points                           | 1                                                                                             |
| <b>Actuator</b>                                    |                                                                                               |
| design of the actuating element                    | Flat buttons                                                                                  |
| principle of operation of the actuating element    | momentary contact type                                                                        |
| product extension optional                         |                                                                                               |
| • light source                                     | No                                                                                            |
| • contact module                                   | Yes                                                                                           |
| color of the actuating element                     | black / black                                                                                 |
| material of the actuating element                  | plastic                                                                                       |
| shape of the actuating element                     | oval                                                                                          |
| marking of the actuating element                   | Customized labeling, text in lower case/capital letters, all words start with capital letters |
| <b>Front ring</b>                                  |                                                                                               |
| product component front ring                       | Yes                                                                                           |
| design of the front ring                           | Standard                                                                                      |
| material of the front ring                         | Metal, matt                                                                                   |
| color of the front ring                            | sand gray                                                                                     |
| <b>General technical data</b>                      |                                                                                               |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                       |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                    |
| shock resistance                                   |                                                                                               |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                              |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                           |
| vibration resistance                               |                                                                                               |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                             |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                           |
| operating frequency maximum                        | 3 600 1/h                                                                                     |
| mechanical service life (operating cycles) typical | 2 000 000                                                                                     |
| reference code according to IEC 81346-2            | S                                                                                             |
| Substance Prohibitance (Date)                      | 10/01/2014                                                                                    |
| Weight                                             | 0.02 kg                                                                                       |
| <b>Ambient conditions</b>                          |                                                                                               |
| ambient temperature                                |                                                                                               |
| • during operation                                 | -25 ... +70 °C                                                                                |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                    |
| height                                                         | 57.9 mm                                                            |
| width                                                          | 29.9 mm                                                            |
| shape of the installation opening                              | round                                                              |
| mounting diameter                                              | 22.3 mm                                                            |
| positive tolerance of installation diameter                    | 0.4 mm                                                             |
| mounting height                                                | 14.4 mm                                                            |
| installation width                                             | 29.9 mm                                                            |
| installation depth                                             | 25.7 mm                                                            |
| <b>Approvals Certificates</b>                                  |                                                                    |
| General Product Approval                                       | Test Certificates                                                  |



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

|                              |                                             |
|------------------------------|---------------------------------------------|
| other                        | Environment                                 |
| <a href="#">Confirmation</a> | <a href="#">Environmental Confirmations</a> |

#### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
 Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
 Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1030-3AB11-0AA0-Z Y15>  
 Cax online generator  
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1030-3AB11-0AA0-Z Y15>  
 Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/3SU1030-3AB11-0AA0-Z Y15>  
 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1030-3AB11-0AA0-Z Y15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1030-3AB11-0AA0-Z Y15&lang=en)

last modified:

4/2/2025