

Siemens
EcoTech



LED module with integrated LED 6-24 V AC/DC, red, spring-type terminal, for front plate mounting, Z=50-unit packaging



product brand name	SIRIUS ACT
product designation	LED module
product type designation	3SU1
General technical data	
product component	
• diode	Yes
• lamp transformer	No
• light source	Yes
• series resistor	No
insulation voltage rated value	320 V
degree of pollution	3
type of voltage of the operating voltage	AC/DC
• for actuation	AC/DC
surge voltage resistance rated value	4 kV
consumed current maximum	30 mA
protection class IP	
• of the enclosure	IP40
• of the terminal	IP20
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating period typical	100 000 h
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	03/01/2017
SVHC substance name	Lead monoxide (lead oxide) - 1317-36-8 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7
Weight	0.008 kg
operating voltage	
• at AC	
— at 50 Hz rated value	6 ... 24 V
— at 60 Hz rated value	6 ... 24 V
• at DC rated value	6 ... 24 V
relative positive tolerance of the operating voltage	20 %
relative negative tolerance of the operating voltage	20 %

Control circuit/ Control			
inrush current maximum		2 A	
Connections/ Terminals			
type of electrical connection		spring-loaded terminals	
type of connectable conductor cross-sections			
• solid without core end processing		2x (0.25 ... 1.5 mm²)	
• finely stranded with core end processing		2x (0.25 ... 0.75 mm²)	
• finely stranded without core end processing		2x (0.25 ... 1.5 mm²)	
• for AWG cables		2x (24 ... 16)	
connectable conductor cross-section finely stranded with core end processing		0.25 ... 0.75 mm²	
Lamp			
type of light source		LED	
color of the light source		red	
light intensity		450 ... 1 120 mcd	
ATEX			
certificate of suitability			
• ATEX		No	
• IECEX		No	
Ambient conditions			
ambient temperature			
• during operation		-25 ... +70 °C	
• during storage		-40 ... +80 °C	
environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)	
Environmental footprint			
Environmental Product Declaration(EPD)		Yes	
global warming potential [CO2 eq] total		0.787 kg	
global warming potential [CO2 eq] during manufacturing		0.566 kg	
global warming potential [CO2 eq] during operation		0.235 kg	
global warming potential [CO2 eq] after end of life		-0.015 kg	
Siemens Eco Profile (SEP)		Siemens EcoTech	
Installation/ mounting/ dimensions			
fastening method			
• of modules and accessories		Front plate mounting	
height		36 mm	
width		9.8 mm	
depth		29.4 mm	
Approvals Certificates			
General Product Approval		EMV	Test Certificates



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other

Environment

[Confirmation](#)



Siemens
EcoTech



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)



<https://www.siemens.com/ic10>


Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1401-1BG20-3AA0-Z X90>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1401-1BG20-3AA0-Z X90>





last modified:

4/2/2025 