



LED module with integrated LED 6-24V AC/DC white, screw terminal, for floor mounting

product brand name	SIRIUS ACT
product designation	LED module
product type designation	3SU1
General technical data	
product component	
• diode	Yes
• lamp transformer	No
• light source	Yes
• series resistor	No
insulation voltage rated value	320 V
degree of pollution	3
type of voltage of the operating voltage	AC/DC
• for actuation	AC/DC
surge voltage resistance rated value	4 kV
consumed current maximum	30 mA
protection class IP	
• of the enclosure	IP40
• of the terminal	IP20
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating period typical	100 000 h
reference code according to IEC 81346-2	P
Substance Prohibitance (Date)	10/01/2014
SVHC substance name	Lead monoxide (lead oxide) - 1317-36-8 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7
Weight	10 g
operating voltage	
• at AC	
— at 50 Hz rated value	6 ... 24 V
— at 60 Hz rated value	6 ... 24 V
• at DC rated value	6 ... 24 V
relative positive tolerance of the operating voltage	20 %
relative negative tolerance of the operating voltage	20 %


Control circuit/ Control			
inrush current maximum		2 A	
Connections/ Terminals			
type of electrical connection		screw terminal	
type of connectable conductor cross-sections		• solid with core end processing2x (0.5 ... 0.75 mm²) • solid without core end processing2x (1.0 ... 1.5 mm²) • finely stranded with core end processing2x (0.5 ... 1.5 mm²) • finely stranded without core end processing2x (1,0 ... 1,5 mm²) • for AWG cables2x (18 ... 14)	
• solid with core end processing			
• solid without core end processing			
• finely stranded with core end processing			
• finely stranded without core end processing			
connectable conductor cross-section finely stranded with core end processing		0.5 ... 1.5 mm²	
tightening torque with screw-type terminals		0.8 ... 0.9 N·m	
Lamp			
type of light source		LED	
color of the light source		white	
light intensity		900 ... 1 400 mcd	
ATEX			
certificate of suitability		• ATEXNo • IECExNo	
• ATEX			
• IECEx			
Ambient conditions			
ambient temperature		• during operation-25 ... +70 °C • during storage-40 ... +80 °C	
• during operation			
• during storage			
environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)	
Environmental footprint			
Environmental Product Declaration(EPD)		Yes	
global warming potential [CO2 eq] total		0.787 kg	
global warming potential [CO2 eq] during manufacturing		0.566 kg	
global warming potential [CO2 eq] during operation		0.235 kg	
global warming potential [CO2 eq] after end of life		-0.015 kg	
Siemens Eco Profile (SEP)		Siemens EcoTech	
Installation/ mounting/ dimensions			
fastening method		• of modules and accessoriesFloor mounting	
• of modules and accessories			
height		33.2 mm	
width		9.8 mm	
depth		29.4 mm	
Approvals Certificates			
General Product Approval		EMV	Test Certificates




[Type Test Certificates/Test Report](#)

Test Certificates	other	Environment
Special Test Certificate	Confirmation	Environmental Confirmations
		

Further information		
Information on the packaging		
https://support.industry.siemens.com/cs/ww/en/view/109813875		
Information- and Downloadcenter (Catalogs, Brochures,...)		
https://www.siemens.com/ic10		
Industry Mall (Online ordering system)		
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1401-2BG60-1AA0		





last modified:

4/2/2025 