



circuit breaker 3VA5 UL Frame 125 breaking capacity class H 65 kA @ 480 V 2-pole, line protection TM210, FTFM, In=110 A overload protection Ir=110 A permanently set short-circuit protection Ii=10 x In UL489 SB (naval), 50 degrees Celsius cable connection on two sides

| Model                                                                                                                      |                             |
|----------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| product brand name                                                                                                         | SETRON                      |
| product designation                                                                                                        | Molded-case circuit breaker |
| product designation / according to UL file                                                                                 | HEAM                        |
| design of the product                                                                                                      | System protection           |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes                         |
| design of the load switch / according to UL 489 / High-Intensity-Discharge circuit breaker (HID Type)                      | No                          |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)                                | No                          |
| design of the overcurrent release                                                                                          | TM210                       |
| protection function of the overcurrent release                                                                             | LI                          |
| number of poles                                                                                                            | 2                           |
| General technical data                                                                                                     |                             |
| operating voltage / at AC / rated value                                                                                    | 415 V                       |
| power loss [W] / maximum                                                                                                   | 17.2 W                      |
| power loss [W] / for rated value of the current / at AC / in hot operating state / per pole                                | 8.6 W                       |
| mechanical service life (operating cycles) / typical                                                                       | 20 000                      |
| electrical endurance (operating cycles) / at AC-1 / at 380/415 V                                                           | 8 000                       |
| electrical endurance (operating cycles) / at AC-1 / at 690 V                                                               | 4 000                       |
| electrical endurance (operating cycles) / at 480 V                                                                         | 8 000                       |
| electrical endurance (operating cycles) / at 600 V                                                                         | 4 000                       |
| product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof                      | No                          |
| product function                                                                                                           |                             |
| • communication function                                                                                                   | No                          |
| • other measurement function                                                                                               | No                          |
| Net Weight                                                                                                                 | 0.668 kg                    |
| Current                                                                                                                    |                             |
| marking / according to UL 489 / 100%-rated breaker                                                                         | No                          |
| operational current                                                                                                        |                             |
| • at 40 °C                                                                                                                 | 110 A                       |
| • at 45 °C                                                                                                                 | 107 A                       |
| • at 50 °C                                                                                                                 | 105 A                       |
| • at 55 °C                                                                                                                 | 103 A                       |
| • at 60 °C                                                                                                                 | 100 A                       |
| • at 65 °C                                                                                                                 | 98 A                        |
| • at 70 °C                                                                                                                 | 96 A                        |
| Switching capacity according to IEC 60947                                                                                  |                             |
| switching capacity class of the circuit breaker                                                                            | H                           |

|                                                                                               |                                                                                                                                                                |
|-----------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| design of short-circuit protection                                                            | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter |
| <b>Switching capacity according to UL 489</b>                                                 |                                                                                                                                                                |
| current breaking capacity                                                                     |                                                                                                                                                                |
| • at 240 V                                                                                    | 150 kA                                                                                                                                                         |
| • at 480 V                                                                                    | 65 kA                                                                                                                                                          |
| • at 600 Y/347 V                                                                              | 25 kA                                                                                                                                                          |
| <b>Adjustable parameters</b>                                                                  |                                                                                                                                                                |
| adjustable response value setting current ( $I_r$ ) / of the L-trip / with I2t characteristic |                                                                                                                                                                |
| • minimum                                                                                     | 110 A                                                                                                                                                          |
| • maximum                                                                                     | 110 A                                                                                                                                                          |
| adjustable response value delay time ( $t_r$ ) / for L-tripping / with I2t characteristic     |                                                                                                                                                                |
| • minimum                                                                                     | 1 s                                                                                                                                                            |
| • maximum                                                                                     | 1 s                                                                                                                                                            |
| adjustable response value setting current ( $I_i$ ) / for I-tripping                          |                                                                                                                                                                |
| • minimum                                                                                     | 1 100 A                                                                                                                                                        |
| • maximum                                                                                     | 1 100 A                                                                                                                                                        |
| adjustable setting current ( $I_{nN}$ ) / for N-tripping                                      |                                                                                                                                                                |
| • minimum                                                                                     | 0 A                                                                                                                                                            |
| • maximum                                                                                     | 0 A                                                                                                                                                            |
| product function / grounding protection                                                       | No                                                                                                                                                             |
| <b>Mechanical Design</b>                                                                      |                                                                                                                                                                |
| product component                                                                             |                                                                                                                                                                |
| • undervoltage release                                                                        | No                                                                                                                                                             |
| • voltage trigger                                                                             | No                                                                                                                                                             |
| • trip indicator                                                                              | No                                                                                                                                                             |
| height [in]                                                                                   | 5.51 in                                                                                                                                                        |
| height                                                                                        | 140 mm                                                                                                                                                         |
| width [in]                                                                                    | 2 in                                                                                                                                                           |
| type of connectable conductor cross-sections / of the round conductor terminal / stranded     | 1 x (8 AWG - 3/0)                                                                                                                                              |
| width                                                                                         | 50.8 mm                                                                                                                                                        |
| depth [in]                                                                                    | 3.01 in                                                                                                                                                        |
| depth                                                                                         | 76.5 mm                                                                                                                                                        |
| <b>Connections</b>                                                                            |                                                                                                                                                                |
| arrangement of electrical connectors / for main current circuit                               | Front connection                                                                                                                                               |
| type of electrical connection / for main current circuit                                      | circular conductor terminal on both sides                                                                                                                      |
| <b>Auxiliary circuit</b>                                                                      |                                                                                                                                                                |
| number of CO contacts / for auxiliary contacts                                                | 0                                                                                                                                                              |
| <b>Accessories</b>                                                                            |                                                                                                                                                                |
| product extension / optional / motor drive                                                    | No                                                                                                                                                             |
| <b>Environmental conditions</b>                                                               |                                                                                                                                                                |
| protection class IP / on the front                                                            | IP40                                                                                                                                                           |
| ambient temperature                                                                           |                                                                                                                                                                |
| • during operation / minimum                                                                  | -25 °C                                                                                                                                                         |
| • during operation / maximum                                                                  | 70 °C                                                                                                                                                          |
| • during storage / minimum                                                                    | -40 °C                                                                                                                                                         |
| • during storage / maximum                                                                    | 80 °C                                                                                                                                                          |
| reference code / according to IEC 81346-2                                                     | Q                                                                                                                                                              |
| <b>Approvals / Certificates</b>                                                               |                                                                                                                                                                |
| <b>General Product Approval</b>                                                               |                                                                                                                                                                |





[Miscellaneous](#)



[Type Test Certificates/Test Report](#)



Maritime application

other



[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5111-6ED26-1AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA5111-6ED26-1AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA5111-6ED26-1AA0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA5111-6ED26-1AA0)


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





**CB**

