

aux. switch module, rotary op. 2 x leading to "ON" and 1 x leading to "OFF"  
accessory for: 3VA13/14; 3VA20-24



| Model                                                        |                                          |
|--------------------------------------------------------------|------------------------------------------|
| product brand name                                           | SETRON                                   |
| product designation                                          | Auxiliary switch module, rotary operator |
| accessories                                                  | Auxiliary switch module                  |
| General technical data                                       |                                          |
| degree of pollution                                          | 3                                        |
| overvoltage category                                         | III                                      |
| Voltage                                                      |                                          |
| surge voltage resistance                                     | 4 kV                                     |
| operating voltage / at AC / according to CSA and UL          | 230 V                                    |
| operating voltage / at DC / according to CSA and UL          | 24 V                                     |
| operating voltage / at AC / at 50 Hz / rated value / minimum | 230 V                                    |
| operating voltage / at DC / rated value / minimum            | 250 V                                    |
| Current                                                      |                                          |
| thermal current                                              | 5 A                                      |
| operational current                                          |                                          |
| • at AC-12 / at 12 V                                         | 5 A                                      |
| • at AC-12 / at 24 V                                         | 5 A                                      |
| • at AC-12 / at 48 V                                         | 5 A                                      |
| • at AC-12 / at 125 V                                        | 5 A                                      |
| • at AC-12 / at 220/240 V                                    | 5 A                                      |
| • at DC-13 / at 12 V                                         | 0.2 A                                    |
| • at DC-13 / at 24 V                                         | 0.2 A                                    |
| • at DC-13 / at 48 V                                         | 0.2 A                                    |
| • at DC-13 / at 110 V                                        | 0.2 A                                    |
| • at DC-13 / at 250 V                                        | 0.2 A                                    |
| • at AC-15 / at 12 V                                         | 2 A                                      |
| • at AC-15 / at 24 V                                         | 2 A                                      |
| • at AC-15 / at 48 V                                         | 2 A                                      |
| • at AC-15 / at 125 V                                        | 2 A                                      |
| • at AC-15 / at 220/240 V                                    | 2 A                                      |
| Mechanical Design                                            |                                          |
| height                                                       | 41.85 mm                                 |
| width                                                        | 88.5 mm                                  |
| depth                                                        | 70 mm                                    |
| ambient temperature / during operation                       |                                          |
| • minimum                                                    | -25 °C                                   |
| • maximum                                                    | 70 °C                                    |
| ambient temperature / during storage                         |                                          |
| • minimum                                                    | -40 °C                                   |

|                                             |        |
|---------------------------------------------|--------|
| • maximum                                   | 80 °C  |
| <b>ambient temperature / during storage</b> |        |
| • minimum                                   | -40 °C |
| • maximum                                   | 80 °C  |

#### Certificates

|                          |     |
|--------------------------|-----|
| General Product Approval | EMV |
|--------------------------|-----|



[Miscellaneous](#)



|                   |       |             |
|-------------------|-------|-------------|
| Marine / Shipping | other | Environment |
|-------------------|-------|-------------|



[Confirmation](#)

[Miscellaneous](#)

[Miscellaneous](#)



[Environmental Con-  
firmations](#)

#### Environment

[Environmental Con-  
firmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9467-0GX20>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9467-0GX20>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)




[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3VA9467-0GX20](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9467-0GX20)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/20/2023

