



SIMATIC ET 200SP, digital combined module, DI 8x/DQ 8x24 V DC/0.5 A standard, DI: sink input, (sinking input), DQ: source output (sourcing output) suitable for BU type A0, color code CC00, substitute value output for DQ, module diagnostics for: short circuit to L+ and M, wire break, supply voltage

General information	
Product type designation	DI 8x/DQ 8x24VDC/0,5A ST
HW functional status	FS01
Firmware version	V1.0
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V18 or higher with HSP 0401
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.42
Operating mode	
• DI	Yes
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSO	No
Redundancy	
• Redundancy capability	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	35 mA; without load
output voltage / header	
Rated value (DC)	24 V
Power loss	
Power loss, typ.	1 W
Address area	
Address space per module	
• Inputs	1 byte; + 1 byte for QI information
• Outputs	1 byte
Hardware configuration	
Automatic encoding	Yes

• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0 with AUX terminals or potential distributor module
• 3-wire connection	BU type A0 with AUX terminals or potential distributor module
Digital inputs	
Number of digital inputs	8
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+11 to +30V
Input current	
• for signal "1", typ.	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
— at "0" to "1", min.	0.05 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.05 ms
— at "1" to "0", max.	20 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Digital outputs	
Type of digital output	Source output (PNP, current-sourcing)
Number of digital outputs	8
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
output type acc. to IEC 61131, type 0.5	Yes
Short-circuit protection	Yes; Electronic
• Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	Typ. L+ (-50 V)
Controlling a digital input	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• with inductive load, max.	0.5 A; max. 1 H inductance
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 kΩ
Output voltage	
• for signal "1", min.	L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A
• for signal "1" permissible range, max.	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", max.	50 μs
• "1" to "0", max.	100 μs
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load (acc. to IEC 60947-5-1, DC13), max.	0.1 Hz; higher frequencies are possible, see Equipment Manual "Maximum permitted switching frequency of inductive loads"

• on lamp load, max.	10 Hz		
Total current of the outputs			
• Current per channel, max.	0.5 A		
• Current per module, max.	4 A		
Total current of the outputs (per module)			
horizontal installation			
— up to 60 °C, max.	4 A		
vertical installation			
— up to 50 °C, max.	4 A		
Cable length			
• shielded, max.	1 000 m		
• unshielded, max.	600 m		
Encoder			
Connectable encoders			
• 2-wire sensor	Yes		
— permissible quiescent current (2-wire sensor), max.	1.5 mA		
Interrupts/diagnostics/status information			
Diagnostics function	Yes		
Substitute values connectable	Yes		
Alarms			
• Diagnostic alarm	Yes		
Diagnoses			
• Monitoring the supply voltage	Yes		
• Wire-break	Yes; module-by-module, for DI: optional protective circuit for preventing wire-break diagnostics in the case of simple encoder contacts: 25 kOhm to 45 kOhm		
• Short-circuit to M	Yes; module-by-module for DQ		
• Short-circuit to L+	Yes; module-by-module for DQ		
• Group error	Yes		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	No		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	No		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	No		
Isolation			
Isolation tested with	707 V DC (type test)		
Standards, approvals, certificates			
Suitable for safety functions	No		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Weights			
Weight, approx.	30 g		
Classifications			
		Version	Classification

eClass	14	27-24-26-04
eClass	12	27-24-26-04
eClass	9.1	27-24-26-04
eClass	9	27-24-26-04
eClass	8	27-24-26-04
eClass	7.1	27-24-26-04
eClass	6	27-24-26-04
ETIM	9	EC001599
ETIM	8	EC001599
ETIM	7	EC001599

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)

[KC](#)

[Miscellaneous](#)



General Product Approval	EMV	For use in hazardous locations
--------------------------	-----	--------------------------------



[KC](#)



[FM](#)

[CCC-Ex](#)



For use in hazardous locations	Maritime application
--------------------------------	----------------------



[Miscellaneous](#)



[NK / Nippon Kaiji Kyokai](#)

Maritime application	Environment
----------------------	-------------



[CCS \(China Classification Society\)](#)



last modified: 5/16/2025