

SCALANCE XR324-12M TS; Managed IE switch, 19" rack; 12x 100/1000 Mbit/s 2-port media modules, electrical or optical; LED diagnostics; error signaling Contact; Select/set pushbutton, PROFINET IO device, network management, Integrated redundancy manager, office features (RSTP, VLAN, IGMP,..) C-PLUG in scope of supply; Power supply 24 V DC; Ports in the front.



product type designation	
product brand name	SCALANCE
product type designation	XR324-12M TS
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / integrated	
number of 100 Mbit/s ST(BFOC) ports	
• for multimode	24
number of 100 Mbit/s SC ports	
• for multimode	24
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for media module	12
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage supply / redundant power supply unit	No
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	44 W
• supply voltage / 1 / rated value	19.2 ... 28.8 V
• consumed current / 1 / maximum	1.8 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	F 5 A / 125 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C












<ul style="list-style-type: none"> • during storage • during transport • note 	-40 ... +85 °C -40 ... +85 °C Reduced operating temperature through the use of media modules (-40 °C to +70 °C) or SFP plug-in transceivers (-40 °C to +60 °C). If the device is installed in the vertical position, the maximum operating temperature is reduced to +50 °C.
relative humidity <ul style="list-style-type: none"> • at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	19-inch rack
number of modular height units / relating to 19-inch cabinet	1
width	483 mm
height	44 mm
depth	305 mm
net weight	5.5 kg
product feature / conformal coating	Yes
fastening method	When used in shipbuilding, the device must be secured in the 19" rack at four points
<ul style="list-style-type: none"> • 19-inch installation • 35 mm DIN-rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting 	Yes No No No No
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of ≤ 0.31-s	100
cascading in cases of star topology	any (depending only on signal propagation time)
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> • CLI • web-based management • MIB support • TRAPs via email • configuration with STEP 7 • RMON • port mirroring • multiport mirroring • CoS • PROFINET IO diagnosis • switch-managed 	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
PROFINET conformity class	B
protocol / is supported	
<ul style="list-style-type: none"> • Telnet • HTTP • HTTPS • TFTP • FTP • BOOTP • GMRP • DCP • LLDP • SNMP v1 • SNMP v2 • SNMP v3 • IGMP (snooping/querier) 	Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes Yes
identification & maintenance function	
<ul style="list-style-type: none"> • I&M0 - device-specific information • I&M1 - higher level designation/location designation 	Yes Yes
product functions / diagnostics	
product function	

<ul style="list-style-type: none"> • port diagnostics 	Yes
<ul style="list-style-type: none"> • statistics Packet Size 	Yes
<ul style="list-style-type: none"> • statistics packet type 	Yes
<ul style="list-style-type: none"> • error statistics 	Yes
<ul style="list-style-type: none"> • SysLog 	Yes
product functions / VLAN	
product function	
<ul style="list-style-type: none"> • VLAN - port based 	Yes
<ul style="list-style-type: none"> • VLAN - protocol-based 	No
<ul style="list-style-type: none"> • VLAN - IP-based 	No
<ul style="list-style-type: none"> • VLAN dynamic 	Yes
number of VLANs / maximum	255
number of VLANs - dynamic / maximum	255
product functions / DHCP	
product function	
<ul style="list-style-type: none"> • DHCP client 	Yes
<ul style="list-style-type: none"> • DHCP Option 82 	Yes
<ul style="list-style-type: none"> • DHCP Option 66 	Yes
<ul style="list-style-type: none"> • DHCP Option 67 	Yes
product functions / redundancy	
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • ring redundancy 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
<ul style="list-style-type: none"> • redundancy procedure STP 	Yes
<ul style="list-style-type: none"> • redundancy procedure RSTP 	Yes
<ul style="list-style-type: none"> • redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> • passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • STP/RSTP 	Yes
<ul style="list-style-type: none"> • STP 	Yes
<ul style="list-style-type: none"> • RSTP 	Yes
<ul style="list-style-type: none"> • MSTP 	Yes
<ul style="list-style-type: none"> • RSTP big network support 	Yes
<ul style="list-style-type: none"> • LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
<ul style="list-style-type: none"> • IEEE 1588 profile default 	Yes
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • UKCA marking 	Yes
<ul style="list-style-type: none"> • KC approval 	Yes
<ul style="list-style-type: none"> • Regulatory Compliance Mark (RCM) 	Yes
standard	

<ul style="list-style-type: none"> • for EMC interference emission • for immunity to EMC • for safety / from CSA and UL 	EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005 UL 60950-1, CSA C22.2 No. 60950-1-03
standards, specifications, approvals / hazardous environments	
certificate of suitability <ul style="list-style-type: none"> • ATEX • UKEX • IECEX • ULhazloc approval • CCC / for hazardous zone according to GB standard • FM registration 	Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / other	
certificate of suitability <ul style="list-style-type: none"> • railway application in accordance with EN 50155 • railway application in accordance with EN 50121-4 • fire protection in accordance with EN 45545-2 • RoHS conformity 	Yes Yes Yes Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / marine classification	
Marine classification association <ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA) 	Yes Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq] <ul style="list-style-type: none"> • total • during manufacturing • during operation • after end of life 	698.41 kg 225.96 kg 471.6 kg 0.85 kg
product functions / general	
MTBF	25 a
reference code <ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	KF KFE
Warranty period	5 a
further information / internet links	
internet link <ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit

www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

Approvals / Certificates

General Product Approval			EMV	For use in hazardous locations	
	Declaration of Conformity			KC	
For use in hazardous locations		Test Certificates		Marine / Shipping	
	FM	CCC-Ex	Type Test Certificates/Test Report		
Marine / Shipping			Railway	Environment	
		NK / Nippon Kaiji Kyokai		Confirmation	

last modified:

4/2/2025 