




|                                         |                                                 |
|-----------------------------------------|-------------------------------------------------|
| product brand name                      | SIRIUS ACT                                      |
| product designation                     | Indicator lights                                |
| design of the product                   | Complete unit                                   |
| product type designation                | 3SU1                                            |
| product line                            | Metal, shiny, 22 mm                             |
| manufacturer's article number           |                                                 |
| • of supplied LED module                | <a href="#">3SU1401-1BB60-3AA0</a>              |
| • of the supplied holder                | <a href="#">3SU1550-0AA10-0AA0</a>              |
| • of supplied repeater                  | <a href="#">3SU1051-6AA60-0AA0</a>              |
| Enclosure                               |                                                 |
| number of command points                | 1                                               |
| Actuator                                |                                                 |
| product extension optional light source | Yes                                             |
| color                                   |                                                 |
| • of the actuating element              | white                                           |
| material of the actuating element       | plastic                                         |
| shape of the actuating element          | round                                           |
| outer diameter of the actuating element | 29.45 mm                                        |
| marking of the actuating element        | Customized labeling, text in lower case letters |
| Front ring                              |                                                 |
| product component front ring            | No                                              |
| Holder                                  |                                                 |
| material of the holder                  | Plastic                                         |
| Display                                 |                                                 |
| number of LED modules                   | 1                                               |
| General technical data                  |                                                 |
| product component light source          | Yes                                             |
| insulation voltage rated value          | 320 V                                           |
| degree of pollution                     | 3                                               |
| surge voltage resistance rated value    | 4 kV                                            |
| protection class IP                     | IP66, IP67, IP69(IP69K)                         |
| protection class IP of the terminal     | IP20                                            |
| degree of protection NEMA rating        | 1, 2, 3, 3R, 4, 4X, 12, 13                      |
| shock resistance                        |                                                 |
| • according to IEC 60068-2-27           | sinusoidal half-wave 15g / 11 ms                |
| vibration resistance                    |                                                 |
| • according to IEC 60068-2-6            | 10 ... 500 Hz: 5g                               |

|                                                                                                                                                                                                                                                            |                                                                                                                                          |                   |                      |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-------------------|----------------------|
| reference code according to IEC 81346-2                                                                                                                                                                                                                    | P                                                                                                                                        |                   |                      |
| Substance Prohibittance (Date)                                                                                                                                                                                                                             | 10/01/2014                                                                                                                               |                   |                      |
| Weight                                                                                                                                                                                                                                                     | 0.074 kg                                                                                                                                 |                   |                      |
| Supply voltage                                                                                                                                                                                                                                             |                                                                                                                                          |                   |                      |
| type of voltage of the supply voltage of the light source                                                                                                                                                                                                  | AC/DC                                                                                                                                    |                   |                      |
| supply voltage of the light source at AC <ul style="list-style-type: none"><li>at 50 Hz rated value</li><li>at 60 Hz rated value</li><li>at 60 Hz rated value</li></ul>                                                                                    | 24 V<br>24 V<br>24 ... 24 V                                                                                                              |                   |                      |
| supply voltage of the light source at DC rated value <ul style="list-style-type: none"><li></li><li></li></ul>                                                                                                                                             | 24 V<br>24 ... 24 V                                                                                                                      |                   |                      |
| relative negative tolerance of the supply voltage                                                                                                                                                                                                          | 30 %                                                                                                                                     |                   |                      |
| relative positive tolerance of the supply voltage                                                                                                                                                                                                          | 25 %                                                                                                                                     |                   |                      |
| Control circuit/ Control                                                                                                                                                                                                                                   |                                                                                                                                          |                   |                      |
| inrush current maximum                                                                                                                                                                                                                                     | 2 A                                                                                                                                      |                   |                      |
| Connections/ Terminals                                                                                                                                                                                                                                     |                                                                                                                                          |                   |                      |
| type of electrical connection <ul style="list-style-type: none"><li>of modules and accessories</li></ul>                                                                                                                                                   | other<br>Spring-type terminal                                                                                                            |                   |                      |
| type of connectable conductor cross-sections <ul style="list-style-type: none"><li>solid without core end processing</li><li>finely stranded with core end processing</li><li>finely stranded without core end processing</li><li>for AWG cables</li></ul> | 2x (0.25 ... 1.5 mm²)<br>2x (0.25 ... 0.75 mm²)<br>2x (0.25 ... 1.5 mm²)<br>2x (24 ... 16)                                               |                   |                      |
| tightening torque of the screws in the bracket                                                                                                                                                                                                             | 1 ... 1.2 N·m                                                                                                                            |                   |                      |
| Lamp                                                                                                                                                                                                                                                       |                                                                                                                                          |                   |                      |
| type of light source                                                                                                                                                                                                                                       | LED                                                                                                                                      |                   |                      |
| color of the light source                                                                                                                                                                                                                                  | white                                                                                                                                    |                   |                      |
| light intensity                                                                                                                                                                                                                                            | 900 ... 1 400 mcd                                                                                                                        |                   |                      |
| Ambient conditions                                                                                                                                                                                                                                         |                                                                                                                                          |                   |                      |
| ambient temperature <ul style="list-style-type: none"><li>during operation</li><li>during storage</li></ul>                                                                                                                                                | -25 ... +70 °C<br>-40 ... +80 °C                                                                                                         |                   |                      |
| environmental category during operation according to IEC 60721                                                                                                                                                                                             | 3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |                   |                      |
| Environmental footprint                                                                                                                                                                                                                                    |                                                                                                                                          |                   |                      |
| Environmental Product Declaration(EPD)                                                                                                                                                                                                                     | Yes                                                                                                                                      |                   |                      |
| global warming potential [CO2 eq] total                                                                                                                                                                                                                    | 0.593 kg                                                                                                                                 |                   |                      |
| global warming potential [CO2 eq] during manufacturing                                                                                                                                                                                                     | 0.625 kg                                                                                                                                 |                   |                      |
| global warming potential [CO2 eq] during operation                                                                                                                                                                                                         | 0.235 kg                                                                                                                                 |                   |                      |
| global warming potential [CO2 eq] after end of life                                                                                                                                                                                                        | -0.267 kg                                                                                                                                |                   |                      |
| Siemens Eco Profile (SEP)                                                                                                                                                                                                                                  | Siemens EcoTech                                                                                                                          |                   |                      |
| Installation/ mounting/ dimensions                                                                                                                                                                                                                         |                                                                                                                                          |                   |                      |
| fastening method <ul style="list-style-type: none"><li>of modules and accessories</li></ul>                                                                                                                                                                | front plate mounting<br>Front plate mounting                                                                                             |                   |                      |
| height                                                                                                                                                                                                                                                     | 40 mm                                                                                                                                    |                   |                      |
| width                                                                                                                                                                                                                                                      | 30 mm                                                                                                                                    |                   |                      |
| shape of the installation opening                                                                                                                                                                                                                          | round                                                                                                                                    |                   |                      |
| mounting diameter                                                                                                                                                                                                                                          | 22.3 mm                                                                                                                                  |                   |                      |
| positive tolerance of installation diameter                                                                                                                                                                                                                | 0.4 mm                                                                                                                                   |                   |                      |
| mounting height                                                                                                                                                                                                                                            | 11.8 mm                                                                                                                                  |                   |                      |
| installation width                                                                                                                                                                                                                                         | 29.5 mm                                                                                                                                  |                   |                      |
| installation depth                                                                                                                                                                                                                                         | 49.7 mm                                                                                                                                  |                   |                      |
| Approvals Certificates                                                                                                                                                                                                                                     |                                                                                                                                          |                   |                      |
| General Product Approval                                                                                                                                                                                                                                   |                                                                                                                                          | Test Certificates | Maritime application |



[Type Test Certificates/Test Report](#)



[Confirmation](#)Siemens  
EcoTech

## Environment

[Environmental Confirmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1152-6AA60-3AA0-Z Y12>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1152-6AA60-3AA0-Z Y12>

Service&amp;Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1152-6AA60-3AA0-Z Y12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1152-6AA60-3AA0-Z Y12&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1152-6AA60-3AA0-Z Y12&lang=en)