

AS-i compact module K45 digital 4 DQ, IP67 4 x output, 1 A 24 V DC maximal 3 A for all outputs 4 x M12 socket Mounting plate 3RK1901-2EA00 or 3RK1901-2DA00 must be ordered separately

General technical data

design of the product	digital I/O modules for operation in the field, IP67 - K45
Type	4 outputs
design of the slave type	standard slave
I/O configuration	8
ID/ID2 code	0/F
Number I/O sockets	4
type of electrical connection of the inputs and outputs	M12 screw-type terminals
AS interface total current input max	45 mA
operating voltage according to AS-Interface specification	26.5 ... 31.6 V
Ground terminal	Using PIN5 on the M12 sockets. Outgoing via flat tab sleeve (2.8 x 0.8 mm form A)
Addressing	front addressing socket
AS interface Connection Polarity reversal protection	built-in
Delivery note	the modules are delivered without mounting plate
Note 1	An external additional supply (AUX POWER) of 20 to 30 V DC is required for the supply of the output circuits. The additional supply must comply with VDE 0106 (PELV), protection class III.

Inputs

number of digital inputs	0
type of connection technology	2- and 3-wire technology
Input circuit	PNP transistor
Inputs sensor supply using AS-Interface	short-circuit and overload resistant

Outputs

number of digital outputs	4
type of voltage of output voltages	DC
Outputs external power supply 24 V DC	using black AS-Interface flat cable
ampacity of the semiconductor output at DC-13 at 24 V	1 A
Outputs aggregate current max	3 A
type of switching output	PNP transistor
design of the pin assignment of the outputs	standard assignment
Outputs socket assignment	3 = "-", 4 = output, 5 = ground terminal
property of the output short-circuit proof	Yes
Outputs - short-circuit protection - induction protection - watchdog	built-in built-in built-in

Display

Status display display of I/Os	yellow LED
--	------------

- display of Uaux
- display of AS-Interface/diagnostics

green LED
green/red dual LED

Assignment of the data bits

Assignment of data bits

- socket
- socket 2
- socket 3
- socket 4

PIN 4 = OUT1 (D0)
PIN 4 = OUT2 (D1)
PIN 4 = OUT3 (D2)
PIN 4 = OUT4 (D3)

Ambient conditions

ambient temperature

- during operation
- during storage

-25 ... +85 °C
-40 ... +85 °C

protection class IP

IP67

Mechanical data

width

45 mm

height

80 mm

depth

30 mm

fastening method

standard rail mounting/wall mounting using mounting plate for K45 compact module

shock resistance

15g / 11 ms

Certificates/ approvals

General Product Approval

EMV

Maritime application



Maritime application

other

Environment

Industrial Communication



[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1100-1CQ20-0AA3>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1100-1CQ20-0AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1100-1CQ20-0AA3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1100-1CQ20-0AA3&lang=en



last modified:

4/1/2025 