

SIPLUS HMI KP700 Comfort based on 6AV2124-1GC01-0AX0 with conformal coating, 0...+50 °C,



Figure similar

General information	
Product type designation	KP700 Comfort
based on	6AV2124-1GC01-0AX0
Display	
Design of display	TFT
Screen diagonal	7 in
Display width	152.4 mm
Display height	91.4 mm
Number of colors	16 777 216
Resolution (pixels)	
• Horizontal image resolution	800 pixel
• Vertical image resolution	480 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	80 000 h
• Backlight dimmable	Yes; 0-100 %
Control elements	
Keyboard fonts	
• Function keys	
— Number of function keys	24
— Number of function keys with LEDs	24
• Keys with LED	Yes
• System keys	Yes
• Numeric keyboard	Yes
• alphanumeric keyboard	Yes; similar to mobile phone
Touch operation	
• Design as touch screen	No; without
Expansions for operator control of the process	
• DP direct LEDs (LEDs as S7 output I/O)	
— F1...Fx	24
• Direct keys (keys as S7 input I/O)	
— F1...Fx	24
• Direct keys (touch buttons as S7 input I/O)	0
Installation type/mounting	
Mounting position	vertical
Wall mounting/direct mounting	No
Mounting in portrait format possible	No
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°

Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	0.5 A
Starting current inrush I _{st}	0.5 A ² s
Power	
Active power input, typ.	12 W
Processor	
Processor type	X86
Memory	
Flash	Yes
RAM	Yes
Memory available for user data	12 Mbyte
Type of output	
Info LED	Yes
Power LED	No
Error LED	No
Acoustics	
• Buzzer	No
• Speaker	Yes
Time of day	
Clock	
• Hardware clock (real-time)	Yes
• Software clock	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
Interfaces	
Number of industrial Ethernet interfaces	1; 2 ports (switch)
Number of RS 485 interfaces	1; RS 422 / 485 combined
Number of RS 422 interfaces	1
Number of RS 232 interfaces	0
Number of USB interfaces	2; USB 2.0
• USB Mini B	1; 5-pole
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	2
With software interfaces	No
Industrial Ethernet	
• Industrial Ethernet status LED	2
• Number of ports of the integrated switch	2
Protocols	
PROFINET	Yes
Supports protocol for PROFINET IO	Yes
IRT	Yes; As of WinCC V12
PROFIBUS	Yes
EtherNet/IP	Yes
MPI	Yes
Protocols (Ethernet)	
• TCP/IP	Yes
• DHCP	Yes
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
WEB characteristics	
• HTTP	Yes
• HTTPS	Yes

• HTML	Yes
• XML	Yes
• CSS	Yes
• Active X	Yes
• JavaScript	Yes
• Java VM	No
Redundancy mode	
Media redundancy	
— MRP	Yes; As of WinCC V12
Further protocols	
• CAN	No
• MODBUS	Yes
Interrupts/diagnostics/status information	
Diagnoses	
• Diagnostic information readable	Yes; S7 controller
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
Degree and class of protection	
IP (at the front)	IP65
IP (rear)	IP20
NEMA (front)	
• Enclosure Type 4 at the front	Yes
• Enclosure Type 4x at the front	Yes
Ambient conditions	
Ambient temperature during operation	
Operation (vertical installation)	
— For vertical installation, min.	0 °C; = Tmin
— For vertical installation, max.	50 °C; = Tmax
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C; = Tmin
— At maximum tilt angle, max.	40 °C; = Tmax
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C; = Tmin
— For vertical installation, max.	40 °C; = Tmax
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C; = Tmin
— At maximum tilt angle, max.	35 °C; = Tmax
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
Relative humidity	
• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation/frost (no commissioning under condensation conditions)
Resistance	
Coolants and lubricants	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
Use on ships/at sea	
— to biologically active substances according to EN	Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on

60721-3-6 — to chemically active substances according to EN 60721-3-6 — to mechanically active substances according to EN 60721-3-6	request Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); * Yes; Class 6S3 incl. sand, dust; *
Usage in industrial process technology	
— Against chemically active substances acc. to EN 60654-4 — Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Class 3 (excluding trichlorethylene) Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
Remark	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
Conformal coating	
- Coatings for printed circuit board assemblies acc. to EN 61086 - Protection against fouling acc. to EN 60664-3 - Military testing according to MIL-I-46058C, Amendment 7 - Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Class 2 for high reliability Yes; Type 1 protection Yes; Discoloration of coating possible during service life Yes; Conformal coating, Class A
Operating systems	
proprietary	No
pre-installed operating system	
Windows CE	Yes
configuration / header	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
Configuration software	
- STEP 7 Basic (TIA Portal) - STEP 7 Professional (TIA Portal) - WinCC flexible Compact - WinCC flexible Standard - WinCC flexible Advanced - WinCC Basic (TIA Portal) - WinCC Comfort (TIA Portal) - WinCC Advanced (TIA Portal) - WinCC Professional (TIA Portal)	No No No No No No Yes; from V11 Yes; from V11 Yes; from V11
Languages	
Online languages	
Number of online/runtime languages	32
Project languages	
Languages per project	32
Functionality under WinCC (TIA Portal)	
Libraries	Yes
Applications/options	
- Web browser - Pocket Word - Pocket Excel - PDF Viewer - Media Player - SIMATIC WinCC Sm@rtServer - SIMATIC WinCC Audit	Yes Yes Yes Yes Yes Yes Yes
Number of Visual Basic Scripts	Yes
Task planner	
- time-controlled - task-controlled	Yes Yes
Help system	

• Number of characters per info text	70
Message system	
• Number of alarm classes	32
• Bit messages	Yes
— Number of bit messages	4 000
• Analog messages	Yes
— Number of analog messages	200
• S7 alarm number procedure	Yes
• System messages HMI	Yes
• System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ...)	Yes
• Number of characters per message	80
• Number of process values per message	8
• Acknowledgment groups	Yes
• Message indicator	Yes
• Message buffer	
— Number of entries	1 024
— Circulating buffer	Yes
— retentive	Yes
— maintenance-free	Yes
Recipe management	
• Number of recipes	300
• Data records per recipe	500
• Entries per data record	1 000
• Size of internal recipe memory	2 Mbyte
• Recipe memory expandable	Yes
Variables	
• Number of variables per device	2 048
• Number of variables per screen	400
• Limit values	Yes
• Multiplexing	Yes
• Structures	Yes
• Arrays	Yes
Images	
• Number of configurable images	500
• Permanent window/default	Yes
• Global image	Yes
• Pop-up images	Yes
• Slide-in images	Yes
• Image selection by PLC	Yes
• Image number in the PLC	Yes
Image objects	
• Number of objects per image	400
• Text fields	Yes
• I/O fields	Yes
• Graphic I/O fields (graphics list)	Yes
• Symbolic I/O fields (text list)	Yes
• Date/time fields	Yes
• Switches	Yes
• Buttons	Yes
• Graphic display	Yes
• Icons	Yes
• Geometric objects	Yes
Complex image objects	
• Number of complex objects per screen	20
• Alarm view	Yes
• Trend view	Yes
• User view	Yes
• Status/control	Yes
• Sm@rtClient view	Yes
• Recipe view	Yes

• f(x) trend view	Yes
• System diagnostics view	Yes
• Media Player	Yes
• HTML browser	Yes
• PDF display	Yes
• IP camera display	Yes
• Bar graphs	Yes
• Sliders	Yes
• Pointer instruments	Yes
• Analog/digital clock	Yes
Lists	
• Number of text lists per project	500
• Number of entries per text list	500
• Number of graphics lists per project	500
• Number of entries per graphics list	500
Archiving	
• Number of archives per device	50
• Number of entries per archive	20 000
• Message archive	Yes
• Process value archive	Yes
• Archiving methods	
— Sequential archive	Yes
— Short-term archive	Yes
• Memory location	
— Memory card	Yes
— USB memory	Yes
— Ethernet	Yes
• Data storage format	
— CSV	Yes
— TXT	Yes
— RDB	Yes
Security	
• Number of user groups	50
• Number of user rights	32
• Number of users	50
• Password export/import	Yes
• SIMATIC Logon	Yes
Logging through printer	
• Alarms	Yes
• Report (shift log)	Yes
• Hardcopy	Yes
• Electronic print to file	Yes; PDF, HTML
Character sets	
• Keyboard fonts	
— US English	Yes
Transfer (upload/download)	
• MPI/PROFIBUS DP	Yes
• USB	Yes
• Ethernet	Yes
• using external storage medium	Yes
Process coupling	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	Yes; with SINUMERIK option package
• SIMOTION	Yes
• Allen Bradley (EtherNet/IP)	Yes
• Allen Bradley (DF1)	Yes

• Mitsubishi (MC TCP/IP) • Mitsubishi (FX) • OMRON (FINS TCP) • OMRON (LINK/Multilink) • Modicon (Modbus TCP/IP) • Modicon (Modbus) • OPC UA Client • OPC UA Server	Yes		
	Yes		
	No		
	Yes		
	Yes		
	Yes		
	Yes		
	Yes		
Service tools/configuration aids			
• Backup/Restore manually	Yes		
• Backup/Restore automatically	Yes		
• Simulation	Yes		
• Device switchover	Yes		
Peripherals/Options			
Printer	Yes		
SIMATIC HMI MM memory card: Multi Media Card	Yes; Up to 128 MB		
SIMATIC HMI SD memory card: Secure Digital memory card	Yes; Up to 2 GB		
SIMATIC HMI CF memory card Compact Flash Card	No		
USB memory	Yes		
SIMATIC IPC USB Flashdrive (USB stick)	Yes; Up to 16 GB		
SIMATIC HMI USB stick	Yes; Up to 8 GB		
Network camera	Yes		
Mechanics/material			
Enclosure material (front)			
• Plastic	No		
• Aluminum	Yes		
• Stainless steel	No		
Dimensions			
Width of the housing front	308 mm		
Height of housing front	204 mm		
Mounting cutout, width	282 mm		
Mounting cutout, height	178 mm		
Overall depth	63 mm		
Weights			
Weight (without packaging)	2.2 kg		
Weight (with packaging)	2.8 kg		
Classifications			
		Version	Classification
	eClass	14	27-33-02-01
	eClass	12	27-33-02-01
	eClass	9.1	27-33-02-01
	eClass	9	27-33-02-01
	eClass	8	27-24-23-02
	eClass	7.1	27-24-23-02
	eClass	6	27-24-23-02
	ETIM	10	EC001412
	ETIM	9	EC001412
	ETIM	8	EC001412
	ETIM	7	EC001412
	IDEA	4	6607
	UNSPSC	15	43-21-15-06
Approvals / Certificates			
General Product Approval			EMV



[Manufacturer Declaration](#)

[China RoHS](#)



[KC](#)

EMV	For use in hazardous locations	Maritime application
-----	--------------------------------	----------------------



[CCC-Ex](#)



last modified:

7/23/2025