



SIMATIC HMI, KTP900 Basic, Basic Panel, Key/touch operation, 9" TFT display, 65536 colors, PROFINET interface, configurable from WinCC Basic V13/ STEP 7 Basic V13, contains open-source software, which is provided free of charge see enclosed CD

General information	
Product type designation	KTP900 Basic color PN
Display	
Design of display	TFT widescreen display, LED backlighting
Screen diagonal	9 in
Display width	198 mm
Display height	111.7 mm
Number of colors	65 536
Resolution (pixels)	
• Horizontal image resolution	800 pixel
• Vertical image resolution	480 pixel
Backlighting	
• MTBF backlighting (at 25 °C)	20 000 h
• Backlight dimmable	Yes
Control elements	
Keyboard fonts	
• Function keys	
— Number of function keys	8
— Number of function keys with LEDs	0
• Keys with LED	No
• System keys	No
• Numeric keyboard	Yes; Onscreen keyboard
• alphanumeric keyboard	Yes; Onscreen keyboard
Touch operation	
• Design as touch screen	Yes; Analog-resistive
Installation type/mounting	
Mounting position	vertical
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	35°
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	230 mA
Starting current inrush I ² t	0.2 A ² ·s
Power	

Active power input, typ.	5.5 W
Processor	
Processor type	ARM
Memory	
Flash	Yes
RAM	Yes
Memory available for user data	10 Mbyte
Type of output	
Acoustics	
• Buzzer	Yes
• Speaker	No
Time of day	
Clock	
• Hardware clock (real-time)	Yes
• Software clock	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
Interfaces	
Number of industrial Ethernet interfaces	1
Number of RS 485 interfaces	0
Number of RS 422 interfaces	0
Number of RS 232 interfaces	0
Number of USB interfaces	1; Up to 16 GB
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	0
With software interfaces	No
Industrial Ethernet	
• Industrial Ethernet status LED	2
Protocols	
PROFINET	Yes
Supports protocol for PROFINET IO	No
IRT	No
PROFIBUS	No
EtherNet/IP	Yes
MPI	No
Protocols (Ethernet)	
• TCP/IP	Yes
• DHCP	Yes
• DCP	Yes
• LLDP	Yes
WEB characteristics	
• HTTP	No
• HTML	No
Redundancy mode	
Media redundancy	
— MRP	No
Further protocols	
• CAN	No
• MODBUS	Yes; Modicon (MODBUS TCP/IP)
Interrupts/diagnostics/status information	
Diagnoses	
• Diagnostic information readable	No
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes
• Limit class B, for use in residential areas	No
Degree and class of protection	
IP (at the front)	IP65

IP (rear)	IP20
NEMA (front)	
• Enclosure Type 4 at the front	Yes
• Enclosure Type 4x at the front	Yes
Standards, approvals, certificates	
CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Use in hazardous areas	
• ATEX Zone 2	No
• ATEX Zone 22	No
• IECEx Zone 2	No
• IECEx Zone 22	No
• cULus Class I Zone 1	No
• cULus Class I Zone 2, Division 2	No
• FM Class I Division 2	No
Marine approval	
• Germanischer Lloyd (GL)	Yes
• American Bureau of Shipping (ABS)	Yes
• Bureau Veritas (BV)	Yes
• Det Norske Veritas (DNV)	Yes
• Lloyds Register of Shipping (LRS)	Yes
• Nippon Kaiji Kyokai (Class NK)	Yes
• Polski Rejestr Statkow (PRS)	No
• Chinese Classification Society (CCS)	No
Ambient conditions	
Ambient temperature during operation	
Operation (vertical installation)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	50 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	40 °C
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	40 °C
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	35 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Relative humidity	
• Operation, max.	90 %; no condensation
Operating systems	
proprietary	Yes
pre-installed operating system	
• Windows CE	No
configuration / header	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
Configuration software	
• STEP 7 Basic (TIA Portal)	Yes; via integrated WinCC Basic (TIA Portal)
• STEP 7 Professional (TIA Portal)	Yes; via integrated WinCC Basic (TIA Portal)
• WinCC flexible Compact	No
• WinCC flexible Standard	No

- WinCC flexible Advanced
- WinCC Basic (TIA Portal)
- WinCC Comfort (TIA Portal)
- WinCC Advanced (TIA Portal)
- WinCC Professional (TIA Portal)

No
Yes
Yes
Yes
Yes

Languages

Online languages

- Number of online/runtime languages

10

Project languages

- Languages per project

32

Functionality under WinCC (TIA Portal)

Libraries

Yes

Applications/options

- Web browser
- SIMATIC WinCC Sm@rtServer

Yes

Yes; Available with WinCC (TIA Portal) V14 or higher

Number of Visual Basic Scripts

No

Task planner

- time-controlled
- task-controlled

No

Yes

Help system

- Number of characters per info text

500

Message system

- Number of alarm classes
- Bit messages
 - Number of bit messages
- Analog messages
 - Number of analog messages
- S7 alarm number procedure
- System messages HMI
- System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ...)
- Number of characters per message
- Number of process values per message
- Acknowledgment groups
- Message indicator
- Message buffer
 - Number of entries
 - Circulating buffer
 - retentive
 - maintenance-free

32

1 000

25

No

Yes

Yes; System message buffer of the SIMATIC S7-1200 and S7-1500

80

8

Yes

Yes

256

Yes

Yes

Yes

Recipe management

- Number of recipes
- Data records per recipe
- Entries per data record
- Size of internal recipe memory
- Recipe memory expandable

50

100

100

256 kbyte

No

Variables

- Number of variables per device
- Number of variables per screen
- Limit values
- Multiplexing
- Structures
- Arrays

800

100

Yes

Yes

No

Yes

Images

- Number of configurable images
- Permanent window/default
- Global image
- Pop-up images
- Slide-in images
- Image selection by PLC
- Image number in the PLC

250

Yes

Yes

No

No

Yes

Yes

Image objects	
• Number of objects per image	100
• Text fields	Yes
• I/O fields	Yes
• Graphic I/O fields (graphics list)	Yes
• Symbolic I/O fields (text list)	Yes
• Date/time fields	Yes
• Switches	Yes
• Buttons	Yes
• Graphic display	Yes
• Icons	Yes
• Geometric objects	Yes
Complex image objects	
• Number of complex objects per screen	10
• Alarm view	Yes
• Trend view	Yes
• User view	Yes
• Status/control	No
• Sm@rtClient view	No
• Recipe view	Yes
• f(x) trend view	No
• System diagnostics view	Yes; System message buffer of the SIMATIC S7-1200 and S7-1500
• Media Player	No
• HTML browser	Yes
• PDF display	No
• IP camera display	No
• Bar graphs	Yes
• Sliders	No
• Pointer instruments	No
• Analog/digital clock	No
Lists	
• Number of text lists per project	300
• Number of entries per text list	100
• Number of graphics lists per project	100
• Number of entries per graphics list	100
Archiving	
• Number of archives per device	2; One message and one process value archive
• Number of entries per archive	10 000
• Message archive	Yes
• Process value archive	Yes
• Archiving methods	
— Sequential archive	Yes
— Short-term archive	Yes
• Memory location	
— Memory card	No
— USB memory	Yes
— Ethernet	No
• Data storage format	
— CSV	No
— TXT	Yes
— RDB	No
Security	
• Number of user groups	50
• Number of user rights	32
• Number of users	50
• Password export/import	Yes
• SIMATIC Logon	No
Character sets	
• Keyboard fonts	
— US English	Yes
Transfer (upload/download)	

• MPI/PROFIBUS DP • USB • Ethernet • using external storage medium	No No Yes Yes		
Process coupling			
• S7-1200 • S7-1500 • S7-200 • S7-300/400 • LOGO! • WinAC • SINUMERIK • SIMOTION • Allen Bradley (EtherNet/IP) • Allen Bradley (DF1) • Mitsubishi (MC TCP/IP) • Mitsubishi (FX) • OMRON (FINS TCP) • OMRON (LINK/Multilink) • Modicon (Modbus TCP/IP) • Modicon (Modbus)	Yes Yes Yes Yes Yes Yes Yes; No access to NCK data Yes Yes No Yes No No No No Yes No		
Service tools/configuration aids			
• Backup/Restore manually • Backup/Restore automatically • Simulation • Device switchover	Yes No Yes Yes		
Peripherals/Options			
Printer	No		
SIMATIC HMI MM memory card: Multi Media Card	No		
SIMATIC HMI SD memory card: Secure Digital memory card	No		
SIMATIC HMI CF memory card Compact Flash Card	No		
USB memory	Yes		
SIMATIC IPC USB Flashdrive (USB stick)	Yes		
SIMATIC HMI USB stick	Yes		
Mechanics/material			
Enclosure material (front) • Plastic • Aluminum • Stainless steel	Yes No No		
Dimensions			
Width of the housing front	267 mm		
Height of housing front	182 mm		
Mounting cutout, width	251 mm		
Mounting cutout, height	166 mm		
Overall depth	39.4 mm		
Weights			
Weight (without packaging)	1 130 g		
Weight (with packaging)	1 393 g		
Classifications			
		Version	Classification
	eClass	14	27-33-02-01
	eClass	12	27-33-02-01
	eClass	9.1	27-33-02-01
	eClass	9	27-33-02-01
	eClass	8	27-24-23-02
	eClass	7.1	27-24-23-02
	eClass	6	27-24-23-02
	ETIM	10	EC001412

ETIM	9	EC001412
ETIM	8	EC001412
ETIM	7	EC001412
IDEA	4	6607
UNSPSC	15	43-21-15-06

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



[KC](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)

[CCS \(China Classification Society\)](#)

Maritime application



last modified:

7/2/2025