



Figure similar

SIMATIC ET 200SP, TM Posinput 1 counter and position decoder module for RS-422 incremental encoder or SSI absolute encoder, 2 DI, 2 DQ suitable for BU type A0, pack quantity: 1 unit

General information	
Product type designation	TM PosInput 1
Firmware version	V2.0
• FW update possible	Yes
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V16 or higher
• STEP 7 configurable/integrated from version	V5.6 (use previous version *6BA00*)
• PROFIBUS from GSD version/GSD revision	GSD Revision 5
• PROFINET from GSD version/GSD revision	GSDML V2.34
Supply voltage	
Rated value (DC)	24 V
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	19.2 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes
Input current	
Current consumption, max.	75 mA; without load
Encoder supply	
Number of outputs	2
5 V encoder supply	
• 5 V	Yes
• Short-circuit protection	Yes; electronic/thermal
• Output current, max.	300 mA; Total current of all encoders
24 V encoder supply	
• 24 V	Yes; L+ (-0.8 V)
• Short-circuit protection	Yes; electronic/thermal
• Output current, max.	300 mA; Total current of all encoders
Power loss	
Power loss, typ.	1.5 W
Address area	
Address space per module	
• Inputs	16 byte; 4 bytes in Fast mode
• Outputs	12 byte; 4 bytes for Motion Control, 0 bytes for Fast mode

Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type B
Digital inputs	
Number of digital inputs	2
Digital inputs, parameterizable	Yes
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Digital input functions, parameterizable	
• Gate start/stop	Yes; only for pulse and incremental encoders
• Capture	Yes
• Synchronization	Yes; only for pulse and incremental encoders
• Freely usable digital input	Yes
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-5 ... +5 V
• for signal "1"	+11 to +30V
• permissible voltage at input, min.	-30 V; -5 V continuous, -30 V brief reverse polarity protection
• permissible voltage at input, max.	30 V
Input current	
• for signal "1", typ.	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; none / 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
for technological functions	
— parameterizable	Yes
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	2
Digital outputs, parameterizable	Yes
Short-circuit protection	Yes; electronic/thermal
• Response threshold, typ.	1 A
Limitation of inductive shutdown voltage to	L+ (-53 V)
Controlling a digital input	Yes
Digital output functions, parameterizable	
• Switching tripped by comparison values	Yes
• Freely usable digital output	Yes
Switching capacity of the outputs	
• with resistive load, max.	0.5 A; Per digital output
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	12 kΩ
Output voltage	
• for signal "1", min.	23.2 V; L+ (-0.8 V)
Output current	
• for signal "1" rated value	0.5 A; Per digital output
• for signal "1" permissible range, max.	0.6 A; Per digital output
• for signal "1" minimum load current	2 mA
• for signal "0" residual current, max.	0.5 mA
Output delay with resistive load	
• "0" to "1", max.	50 μs
• "1" to "0", max.	50 μs
Switching frequency	
• with resistive load, max.	10 kHz
• with inductive load, max.	0.5 Hz; Acc. to IEC 60947-5-1, DC-13; observe derating curve
• on lamp load, max.	10 Hz

Total current of the outputs	
• Current per module, max.	1 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Encoder signals, incremental encoder (symmetrical)	
• Input voltage	RS 422
• Input frequency, max.	1 MHz
• Counting frequency, max.	4 MHz; with quadruple evaluation
• Cable length, shielded, max.	32 m; at 1 MHz
• Signal filter, parameterizable	Yes
• Incremental encoder with A/B tracks, 90° phase offset	Yes
• Incremental encoder with A/B tracks, 90° phase offset and zero track	Yes
• pulse encoder	Yes
• Pulse encoder with direction	Yes
• pulse encoder with one impulse signal per count direction	Yes
Encoder signals, incremental encoder (asymmetrical)	
• Input voltage	5 V TTL (push-pull encoders only)
• Input frequency, max.	1 MHz
• Counting frequency, max.	4 MHz; with quadruple evaluation
• Signal filter, parameterizable	Yes
• Incremental encoder with A/B tracks, 90° phase offset	Yes
• Incremental encoder with A/B tracks, 90° phase offset and zero track	Yes
• pulse encoder	Yes
• pulse encoder with direction	Yes
• pulse encoder with one impulse signal per count direction	Yes
Encoder signals, absolute encoder (SSI)	
• Input signal	to RS-422
• Telegram length, parameterizable	10 ... 40 bit
• Clock frequency, max.	2 MHz; 125 kHz, 250 kHz, 500 kHz, 1 MHz, 1.5 MHz or 2 MHz
• Binary code	Yes
• Gray code	Yes
• Cable length, shielded, max.	320 m; Cable length, RS-422 SSI absolute encoders, Siemens type 6FX2001-5, 24 V supply: 125 kHz, 320 meters shielded, max.; 250 kHz, 160 meters shielded, max.; 500 kHz, 60 meters shielded, max.; 1 MHz, 20 meters shielded, max. 1.5 MHz, 10 meters shielded, max.; 2 MHz, 8 meters shielded, max.
• Parity bit, parameterizable	Yes
• Monoflop time	16, 32, 48, 64 µs & automatic
• Multiturn	Yes
• Singleturn	Yes
Interface types	
• TTL 5 V	Yes; push-pull encoders only
• RS 422	Yes
Interfaces	
Number of RS 485 interfaces	0
Interrupts/diagnostics/status information	
Substitute values connectable	Yes; Parameterizable
Alarms	
• Diagnostic alarm	Yes
• Hardware interrupt	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes
• Short-circuit	Yes
• A/B transition error at incremental encoder	Yes
• Telegram error at SSI encoder	Yes
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED

• Channel status display • for module diagnostics • Status indicator forward counting (green) • Status indicator backward counting (green)	Yes; green LED Yes; green/red DIAG LED Yes Yes
Integrated Functions	
Counter	Yes
• Number of counters • Counting frequency, max.	1 4 MHz; with quadruple evaluation
Fast mode	Yes
Counting functions	
• Can be used with TO High_Speed_Counter • Continuous counting • Counter response parameterizable • Hardware gate via digital input • Software gate • Event-controlled stop • Synchronization via digital input • Counting range, parameterizable	Yes; only for pulse and incremental encoders Yes Yes Yes Yes Yes Yes Yes
Comparator	
— Number of comparators — Direction dependency — Can be changed from user program	2 Yes Yes
Position detection	
• Incremental acquisition • Absolute acquisition • Suitable for S7-1500 Motion Control	Yes Yes Yes
Measuring functions	
• Measuring time, parameterizable • Dynamic measurement period adjustment • Number of thresholds, parameterizable	Yes Yes 2
Measuring range	
— Frequency measurement, min. — Frequency measurement, max. — Cycle duration measurement, min. — Cycle duration measurement, max.	0.04 Hz 4 MHz 0.25 μ s 25 s
Accuracy	
— Frequency measurement — Cycle duration measurement — Velocity measurement	100 ppm; depending on measuring interval and signal evaluation 100 ppm; depending on measuring interval and signal evaluation 100 ppm; depending on measuring interval and signal evaluation
Potential separation	
Potential separation channels	
• between the channels and backplane bus	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	No
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max. • ceiling installation, min. • ceiling installation, max. • floor installation, min. • floor installation, max.	-30 °C 60 °C; Observe derating -30 °C 50 °C; Observe derating -30 °C 50 °C; Observe derating -30 °C 50 °C; Observe derating
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Decentralized operation	
to SIMATIC S7-300	Yes

to SIMATIC S7-400	Yes
to SIMATIC S7-1200	Yes
to SIMATIC S7-1500	Yes
to standard PROFIBUS master	Yes
to standard PROFINET controller	Yes

Dimensions

Width	15 mm
Height	73 mm
Depth	58 mm

Weights

Weight, approx.	45 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-05
eClass	12	27-24-26-05
eClass	9.1	27-24-26-05
eClass	9	27-24-26-05
eClass	8	27-24-26-05
eClass	7.1	27-24-26-05
eClass	6	27-24-26-05
ETIM	10	EC001601
ETIM	9	EC001601
ETIM	8	EC001601
ETIM	7	EC001601
IDEA	4	3567
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval

[Manufacturer Declaration](#)



[Miscellaneous](#)



For use in hazardous locations



[FM](#)



[Miscellaneous](#)

[Type Examination Certificate](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application



[CCS \(China Classification Society\)](#)



last modified:

9/24/2025

