



SIMATIC ET 200SP, BaseUnit BU20-P6+A2+4D, BU type C0, Push-in terminals, with 2 AUX terminals, New load group, WxH: 20 mmx117 mm

General information	
Product type designation	BU type C0
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	See manual
• For P1 and P2 bus	24 V
• For AUX bus	24 V; Equal potential group to P1/P2 bus or PE
• for process terminals	24 V
Rated value (AC)	See manual
• For P1 and P2 bus	230 V
• For AUX bus	230 V; Equal potential group to P1/P2 bus or PE
• for process terminals	230 V
external protection for power supply lines	Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage
Mains filter	
• integrated	No
Current carrying capacity	
up to 60 °C, max.	10 A
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	5 A; 10 A for process terminals 5 and 6
Hardware configuration	
Automatic encoding	Yes
Slots	
• Number of slots	1
Potential separation	
between backplane bus and supply voltage	Yes
between process terminals and supply voltage	Yes
between power bus and supply voltage	No
Isolation	
Isolation tested with	3 100 V DC
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle)	-0.0011 kg

[CO2 eq]

Ambient conditions

Ambient temperature during operation

- horizontal installation, min. -30 °C
- horizontal installation, max. 60 °C
- vertical installation, min. -30 °C
- vertical installation, max. 50 °C

Altitude during operation relating to sea level

- Installation altitude above sea level, max. 2 000 m; On request: Installation altitudes greater than 2 000 m

Accessories

Color coding labels

- for process terminals CC51, CC52
- for AUX terminals CC84 to CC86
- for add-on terminals does not exist

connection method

Terminals

- Terminal type Push-in terminal
- system-integrated shield connection Yes; Optional
- Conductor cross-section, min. 0.14 mm²; AWG 26
- Conductor cross-section, max. 2.5 mm²; AWG 14
- Number of process terminals to I/O module 12; Pro slot
- Number of terminals to AUX bus 0
- Number of add-on terminals 0
- Number of terminals with connection to P1 and P2 bus 0; Pro slot

Dimensions

Width	20 mm
Height	117 mm
Depth	35 mm

Weights

Weight, approx.	47 g
-----------------	------

Classifications

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



[KC](#)



For use in hazardous locations



[CCC-Ex](#)

[FM](#)



[Miscellaneous](#)

Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application

Environment



[CCS \(China Classification Society\)](#)



last modified:

9/19/2025