



SCALANCE X204RNA EEC; redundant network access 2x 100 Mbit/s RJ45 ports; 2x 100 Mbit/s combo ports; LED diagnostics; error signaling contact with set pushbutton; simple power supply; network management; including electronic manual on CD-ROM, C-PLUG optional for PRP network

product type designation	
product brand name	SCALANCE
product type designation	X204RNA EEC
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	2
number of combo ports / with RJ45 interface for optical plug-in transceiver	2
interfaces / other	
number of electrical connections	
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for signaling contact	3-pole terminal block
• for power supply	3-pole terminal block
design of the removable storage	
• C-PLUG	Yes
operating voltage / of the signaling contacts	
• at AC / rated value	230 V
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at AC / maximum	0.1 A
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	6 W
• supply voltage / 1 / rated value	85 ... 276 V
• consumed current / 1 / maximum	0.25 A
• type of electrical connection / 1 / for power supply	3-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	1.25 A
type of voltage / 2 / of the supply voltage	AC
• supply voltage / 2 / rated value	85 ... 276 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C

<ul style="list-style-type: none"> <li>during storage</li> <li>during transport</li> <li>note</li> </ul>	-40 ... +70 °C -40 ... +70 °C A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
relative humidity <ul style="list-style-type: none"> <li>at 25 °C / without condensation / during operation / maximum</li> </ul>	95 %
protection class IP	IP20
<b>design, dimensions and weights</b>	
design	compact
width	70 mm
height	147 mm
depth	123 mm
net weight	0.78 kg
product feature / conformal coating	Yes
fastening method <ul style="list-style-type: none"> <li>35 mm DIN-rail mounting</li> <li>wall mounting</li> <li>S7-300 rail mounting</li> <li>S7-1500 rail mounting</li> </ul>	Yes No No No
<b>product functions / management, configuration, engineering</b>	
product function <ul style="list-style-type: none"> <li>CLI</li> <li>web-based management</li> <li>MIB support</li> <li>TRAPs via email</li> <li>configuration with STEP 7</li> <li>port mirroring</li> <li>multiport mirroring</li> <li>with IRT / PROFINET IO switch</li> <li>PROFINET IO diagnosis</li> <li>switch-managed</li> </ul>	Yes Yes Yes Yes No No No No No No
protocol / is supported <ul style="list-style-type: none"> <li>Telnet</li> <li>HTTP</li> <li>HTTPS</li> <li>TFTP</li> <li>FTP</li> <li>BOOTP</li> <li>GMRP</li> <li>DCP</li> <li>LLDP</li> <li>SNMP v1</li> <li>SNMP v2</li> <li>SNMP v3</li> <li>IGMP (snooping/querier)</li> </ul>	No Yes Yes No No No No Yes No Yes Yes Yes No
identification & maintenance function <ul style="list-style-type: none"> <li>I&amp;M0 - device-specific information</li> <li>I&amp;M1 - higher level designation/location designation</li> </ul>	Yes Yes
<b>product functions / diagnostics</b>	
product function <ul style="list-style-type: none"> <li>port diagnostics</li> <li>statistics Packet Size</li> <li>statistics packet type</li> <li>error statistics</li> </ul>	Yes Yes Yes Yes
<b>product functions / redundancy</b>	
protocol / is supported / Media Redundancy Protocol (MRP)	No
product function <ul style="list-style-type: none"> <li>media redundancy protocol (MRP) with redundancy manager</li> <li>ring redundancy</li> </ul>	No No

<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	No
<ul style="list-style-type: none"> <li>• high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	No
<ul style="list-style-type: none"> <li>• High-availability Seamless Redundancy (HSR)</li> </ul>	No
<ul style="list-style-type: none"> <li>• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• High-availability Seamless Redundancy (HSR) and Parallel Redundancy Protocol (PRP) coupling</li> </ul>	No
<ul style="list-style-type: none"> <li>• passive listening</li> </ul>	No
<b>product functions / security</b>	
protocol / is supported	
<ul style="list-style-type: none"> <li>• SSH</li> </ul>	Yes
<b>product functions / time</b>	
product function	
<ul style="list-style-type: none"> <li>• SICLOCK support</li> </ul>	No
protocol / is supported	
<ul style="list-style-type: none"> <li>• NTP</li> </ul>	No
<ul style="list-style-type: none"> <li>• SNTP</li> </ul>	Yes
<b>standards, specifications, approvals</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>• CE marking</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• UKCA marking</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• cULus approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• KC approval</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Regulatory Compliance Mark (RCM)</li> </ul>	Yes
standard	
<ul style="list-style-type: none"> <li>• for EMC</li> </ul>	IEC 61850, IEEE 1613
<ul style="list-style-type: none"> <li>• for EMC interference emission</li> </ul>	EN 61000-6-4:2001 (Class A)
<ul style="list-style-type: none"> <li>• for immunity to EMC</li> </ul>	EN 61000-6-4:2001
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	UL 508 E85972, CSA C22.2 no. 142-M1987
<b>standards, specifications, approvals / other</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>• railway application in accordance with EN 50155</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• railway application in accordance with EN 50121-4</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• railway application in accordance with EN 50124-1</li> </ul>	No
<ul style="list-style-type: none"> <li>• fire protection in accordance with EN 45545-2</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEC 61850-3</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• IEEE 1613</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• RoHS conformity</li> </ul>	Yes
<b>standards, specifications, approvals / marine classification</b>	
Marine classification association	
<ul style="list-style-type: none"> <li>• Royal Institution of Naval Architects (RINA)</li> </ul>	Yes
<b>product functions / general</b>	
MTBF	67.64 a
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> </ul>	KF
<ul style="list-style-type: none"> <li>• according to IEC 81346-2:2019</li> </ul>	KFE
Warranty period	5 a
product function / is supported / identification link	Yes; acc. to IEC 61406-1:2022
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to website: Selection guide for cables and connectors</li> </ul>	<a href="https://support.industry.siemens.com/cs/ww/en/view/109766358">https://support.industry.siemens.com/cs/ww/en/view/109766358</a>
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> </ul>	<a href="https://www.siemens.com/tstcloud">https://www.siemens.com/tstcloud</a>
<ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>	<a href="https://www.siemens.com/simatic-net">https://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>• to web page: SiePortal</li> </ul>	<a href="https://sieportal.siemens.com/">https://sieportal.siemens.com/</a>
<ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>	<a href="https://www.automation.siemens.com/bilddb">https://www.automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>• to website: CAX-Download-Manager</li> </ul>	<a href="https://www.siemens.com/cax">https://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>security information</b>	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks.

In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit [www.siemens.com/cybersecurity-industry](http://www.siemens.com/cybersecurity-industry). Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under <https://www.siemens.com/cert>. (V4.7)

## Approvals / Certificates

### General Product Approval



[Declaration of Conformity](#)



[China RoHS](#)

### General Product Approval

### EMV

### For use in hazardous locations

### Test Certificates

### Maritime application

[Miscellaneous](#)



[KC](#)

[FM](#)

[Type Test Certificates/Test Report](#)



### Maritime application



[NK / Nippon Kaiji Kyokai](#)



### Railway

[Confirmation](#)

last modified:

8/19/2025