

Plug-in relay 2 W, Width 15 mm, 125 V DC for LZS sockets

product brand name	SIRIUS
product designation	Plug-in relay
product type designation	LZX
General technical data	
consumed active power	420 mW
percental drop-out voltage related to the input voltage	10 %
shock resistance according to IEC 60068-2-27	5g / 11 ms
vibration resistance according to IEC 60068-2-6	30 ... 150 Hz: 5g
operating frequency without load	72 000 1/h
operating frequency with load	360 1/h
switching behavior	monostable
mechanical service life (operating cycles) typical	30 000 000
electrical endurance (operating cycles) at AC-15 at 230 V typical	100 000
thermal current	8 A
reference code according to IEC 81346-2	K
Substance Prohibitance (Date)	05/01/2012
Weight	0.014 kg
Control circuit/ Control	
control supply voltage at DC rated value	110 V
operating range factor control supply voltage rated value at DC	
• initial value	0.9
• full-scale value	1.4
Switching Function	
design of the switching function	changeover switch
Mechanical data	
product component plug-in socket	No
design of the relay operating mechanism	poled
Auxiliary circuit	
type of switching contact	Changeover contact
material of switching contacts	AgNi 90/10
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	2
operational current of auxiliary contacts at AC-15	
• at 250 V	3 A
operational current at DC-13 at 24 V rated value	2 A
operational current of auxiliary contacts at DC-13	
• at 24 V	2 A

Main circuit	
type of voltage	DC
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
• at 24 V	2 A
Connections/ Terminals	
product function removable terminal	No
Installation/ mounting/ dimensions	
mounting position	any
fastening method	base mounting
height	29 mm
width	12.7 mm
depth	19.5 mm
Ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
Further information	

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=LZX:RT424110>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=LZX:RT424110>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:RT424110>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=LZX:RT424110&lang=en





last modified:

4/2/2025 