



Control Power Transformer, 75va, PRI 380/400/415v, SEC 110x220v, International

product brand name	Control Power Transformer
design of the product	Control power voltage
special product feature	Touch safe terminals
General technical data	
weight [lb]	3.5 lb(av)
Height x Width x Depth [in]	2.78 × 3 × 3.79 in
ambient temperature [°F] during operation	-4 ... +104 °F
ambient temperature during operation	-20 ... +40 °C
country of origin	Mexico
operating apparent power rated value	75 VA
Enclosure	
design of the housing	Open
Mounting/wiring	
mounting position	Any
fastening method	Surface mounting
type of electrical connection at output for main current circuit	Screw-type terminals (touchsafe)
type of electrical connection at input for main current circuit	Screw-type terminals (touchsafe)
Inputs/ Outputs	
input variables of primary voltage	380/400/415vac
output dimensions of secondary voltage	110x220vac
phase number of the inputs	1
electrical input frequency	50 ... 60 Hz
input voltage _1	380 V
input voltage _2	400 V
input voltage _3	415 V
phase number of the outputs	1
electrical output frequency	60 ... 50 Hz
output voltage _1 rated value	110 V
output voltage _2 rated value	220 V
certificate of suitability	UL / CSA
Approvals Certificates	
Test Certificates	



www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MTG0075I>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MTG0075I>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:MTG0075I&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/US2:MTG0075I/certificate>

last modified:

5/31/2021 