



power contactor AC-1 275 A / 690 V / 40 °C 3-pole, Uc: 200-277 V AC(50-60 Hz) / DC F-PLC input 24 V DC drive: electronic auxiliary contacts 2 NO + 2 NC main circuit: busbar control and auxiliary circuit: screw terminal

product brand name	SIRIUS
product designation	Contactor
product type designation	3RT14
General technical data	
size of contactor	S6
product extension	<ul style="list-style-type: none"> • function module for communication • auxiliary switch
power loss [W] for rated value of the current	<ul style="list-style-type: none"> • at AC in hot operating state 86.4 W • at AC in hot operating state per pole 28.8 W • without load current share typical 2.8 W
type of calculation of power loss depending on pole	quadratic
insulation voltage	<ul style="list-style-type: none"> • of main circuit with degree of pollution 3 rated value 1 000 V • of auxiliary circuit with degree of pollution 3 rated value 500 V
surge voltage resistance	<ul style="list-style-type: none"> • of main circuit rated value 8 kV • of auxiliary circuit rated value 6 kV
shock resistance at rectangular impulse	<ul style="list-style-type: none"> • at AC 8,5g / 5 ms, 4,2g / 10 ms • at DC 8,5g / 5 ms, 4,2g / 10 ms
shock resistance with sine pulse	<ul style="list-style-type: none"> • at AC 13,4g / 5 ms, 6,5g / 10 ms • at DC 13,4g / 5 ms, 6,5g / 10 ms
mechanical service life (operating cycles)	<ul style="list-style-type: none"> • of contactor typical 10 000 000 • of the contactor with added electronically optimized auxiliary switch block typical 5 000 000 • of the contactor with added auxiliary switch block typical 10 000 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	03/01/2017
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol - 79-94-7 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one - 71868-10-5 Perfluorobutane sulfonic acid (PFBS) and its salts - - Melamine - 108-78-1
Net Weight	3.338 kg
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m

ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-55 ... +80 °C
relative humidity minimum	10 %
relative humidity at 55 °C according to IEC 60068-2-30 maximum	95 %
Main circuit	
number of poles for main current circuit	3
number of NO contacts for main contacts	3
number of NC contacts for main contacts	0
type of voltage for main current circuit	AC
operational current	
• at AC-1	
— up to 690 V at ambient temperature 40 °C rated value	275 A
— up to 690 V at ambient temperature 55 °C rated value	250 A
— up to 690 V at ambient temperature 60 °C rated value	250 A
• at AC-3	
— at 400 V rated value	97 A
— at 690 V rated value	97 A
minimum cross-section in main circuit at maximum AC-1 rated value	140 mm ²
operational current	
• at 1 current path at DC-1	
— at 24 V rated value	250 A
— at 60 V rated value	250 A
— at 110 V rated value	18 A
— at 220 V rated value	3.4 A
— at 440 V rated value	0.8 A
— at 600 V rated value	0.5 A
• with 2 current paths in series at DC-1	
— at 24 V rated value	250 A
— at 60 V rated value	250 A
— at 110 V rated value	250 A
— at 220 V rated value	20 A
— at 440 V rated value	3.2 A
— at 600 V rated value	1.6 A
• with 3 current paths in series at DC-1	
— at 24 V rated value	250 A
— at 60 V rated value	250 A
— at 110 V rated value	250 A
— at 220 V rated value	250 A
— at 440 V rated value	11.5 A
— at 600 V rated value	4 A
• at 1 current path at DC-3 at DC-5	
— at 24 V rated value	250 A
— at 60 V rated value	7.5 A
— at 110 V rated value	2.5 A
— at 220 V rated value	0.6 A
— at 440 V rated value	0.17 A
— at 600 V rated value	0.12 A
• with 2 current paths in series at DC-3 at DC-5	
— at 24 V rated value	250 A
— at 60 V rated value	250 A
— at 110 V rated value	250 A
— at 220 V rated value	2.5 A
— at 440 V rated value	0.65 A
— at 600 V rated value	0.37 A

• with 3 current paths in series at DC-3 at DC-5		
— at 24 V rated value	250 A	
— at 60 V rated value	250 A	
— at 110 V rated value	250 A	
— at 220 V rated value	250 A	
— at 440 V rated value	1.4 A	
— at 600 V rated value	0.75 A	
no-load switching frequency		
• at AC	1 000 1/h	
• at DC	1 000 1/h	
operating frequency at AC-1 maximum	200 1/h	
Control circuit/ Control		
type of voltage	AC/DC	
type of voltage of the control supply voltage	AC/DC	
control supply voltage at AC		
• at 50 Hz rated value	200 ... 277 V	
• at 60 Hz rated value	200 ... 277 V	
control supply voltage at DC rated value	200 ... 277 V	
operating range factor control supply voltage rated value of magnet coil at DC		
• initial value	0.8	
• full-scale value	1.1	
operating range factor control supply voltage rated value of magnet coil at AC		
• at 50 Hz	0.8 ... 1.1	
• at 60 Hz	0.8 ... 1.1	
type of PLC-control input according to IEC 60947-1	Type 1	
consumed current at PLC-control input according to IEC 60947-1 maximum	30 mA	
design of the surge suppressor	with varistor	
apparent pick-up power		
• at minimum rated control supply voltage at AC		
— at 50 Hz	190 VA	
— at 60 Hz	190 VA	
• at maximum rated control supply voltage at AC		
— at 60 Hz	280 VA	
— at 50 Hz	280 VA	
apparent pick-up power of magnet coil at AC		
• at 50 Hz	280 VA	
inductive power factor with closing power of the coil		
• at 50 Hz	0.8	
apparent holding power		
• at minimum rated control supply voltage at DC	2.1 VA	
• at maximum rated control supply voltage at DC	2.8 VA	
apparent holding power		
• at minimum rated control supply voltage at AC		
— at 50 Hz	4.3 VA	
— at 60 Hz	4.3 VA	
• at maximum rated control supply voltage at AC		
— at 50 Hz	5.2 VA	
— at 60 Hz	5.2 VA	
apparent holding power of magnet coil at AC		
• at 50 Hz	4.4 VA	
inductive power factor with the holding power of the coil		
• at 50 Hz	0.5	
closing power of magnet coil at DC	320 W	
holding power of magnet coil at DC	2.8 W	
closing delay		
• at AC	60 ... 75 ms	
• at DC	60 ... 75 ms	

opening delay	115 ... 130 ms
• at AC	115 ... 130 ms
• at DC	
arcning time	10 ... 15 ms
control version of the switch operating mechanism	
Auxiliary circuit	
number of NC contacts for auxiliary contacts	2
• attachable	4
• instantaneous contact	2
number of NO contacts for auxiliary contacts	2
• attachable	4
• instantaneous contact	2
operational current at AC-12 maximum	10 A
operational current at AC-15	
• at 230 V rated value	6 A
• at 400 V rated value	3 A
• at 500 V rated value	2 A
• at 690 V rated value	1 A
operational current at DC-13	
• at 24 V rated value	10 A
• at 48 V rated value	2 A
• at 60 V rated value	2 A
• at 110 V rated value	1 A
• at 125 V rated value	0.9 A
• at 220 V rated value	0.3 A
• at 600 V rated value	0.1 A
contact reliability of auxiliary contacts	1 faulty switching per 100 million (17 V, 1 mA)
Short-circuit protection	
design of the miniature circuit breaker for short-circuit protection of the auxiliary circuit up to 230 V	C characteristic: 10 A; 0.4 kA
design of the fuse link	
• for short-circuit protection of the main circuit	
— with type of coordination 1 required	gG: 355 A (690 V, 100 kA)
— with type of coordination 2 required	gR: 350 A (690 V, 100 kA)
• for short-circuit protection of the auxiliary switch required	gG: 10 A (500 V, 1 kA)
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back
fastening method side-by-side mounting	Yes
fastening method	screw fixing
height	172 mm
width	120 mm
depth	170 mm
required spacing	
• with side-by-side mounting	
— forwards	20 mm
— upwards	10 mm
— downwards	10 mm
— at the side	0 mm
• for grounded parts	
— forwards	20 mm
— upwards	10 mm
— at the side	10 mm
— downwards	10 mm
• for live parts	
— forwards	20 mm
— upwards	10 mm
— downwards	10 mm
— at the side	10 mm

Connections/ Terminals	
type of electrical connection	
• for main current circuit	Connection bar
• for auxiliary and control circuit	screw-type terminals
• at contactor for auxiliary contacts	Screw-type terminals
• of magnet coil	Screw-type terminals
width of connection bar	17 mm
thickness of connection bar	3 mm
diameter of holes	9 mm
number of holes	1
type of connectable conductor cross-sections	
• for AWG cables for main contacts	4 ... 250 kcmil
connectable conductor cross-section for main contacts	
• solid or stranded	25 ... 120 mm ²
• stranded	25 ... 120 mm ²
connectable conductor cross-section for auxiliary contacts	
• solid or stranded	0.5 ... 4 mm ²
• finely stranded with core end processing	0.5 ... 2.5 mm ²
type of connectable conductor cross-sections	
• for auxiliary contacts	
— solid	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²), max. 2x (0.75 ... 4 mm ²)
— solid or stranded	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²), max. 2x (0.75 ... 4 mm ²)
— finely stranded with core end processing	2x (0.5 ... 1.5 mm ²), 2x (0.75 ... 2.5 mm ²)
• for AWG cables for auxiliary contacts	2x (20 ... 16), 2x (18 ... 14), 1x 12
AWG number as coded connectable conductor cross section for auxiliary contacts	18 ... 14
Safety related data	
product function	
• mirror contact according to IEC 60947-4-1	Yes
• positively driven operation according to IEC 60947-5-1	No
• suitable for safety function	Yes
suitability for use safety-related switching OFF	Yes
safe state	off
stop category according to IEC 60204-1	0
proportion of dangerous failures	
• with low demand rate according to SN 31920	40 %
• with high demand rate according to SN 31920	73 %
B10 value with high demand rate according to SN 31920	1 000 000
failure rate [FIT] with low demand rate according to SN 31920	100 FIT
IEC 62061	
Safety Integrity Level (SIL) according to IEC 62061	SIL 2
PFHD with high demand rate according to IEC 62061	4.5E-7 1/h
ISO 13849	
performance level (PL) according to ISO 13849-1	PL c
category according to ISO 13849-1	2
device type according to ISO 13849-1	1
overdimensioning according to ISO 13849-2 necessary	Yes
IEC 61508	
Safety Integrity Level (SIL) according to IEC 61508	2
safety device type according to IEC 61508-2	Type B
PFHD with high demand rate according to IEC 61508	4.5E-7 1/h
PFDAvg with low demand rate according to IEC 61508	0.007
Safe failure fraction (SFF)	93 %
hardware fault tolerance according to IEC 61508	0
T1 value of service life according to IEC 61508	20 a
Electrical Safety	
protection class IP on the front according to IEC 60529	IP00; IP20 with box terminal/cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with box terminal/cover

Approvals Certificates

General Product Approval



CCC



EG-Konf.



KC



EMV	Functional Safety	Test Certificates	other
	Type Examination Certificate	Special Test Certificate	Type Test Certificates/Test Report
Confirmation			
other	Railway	Environment	
Miscellaneous	Special Test Certificate	Environmental Confirmations	

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT1456-6SP36>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT1456-6SP36>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT1456-6SP36&lang=en

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT1456-6SP36>

Characteristic curves

[https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simaris.siemens.com/curves/<mmp_prod_noCOMP=)



